

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE		-40°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +70°C (AT PACKING)
	POWER		—w	CHARACTERISTIC IMPEDANCE	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ENVIRONMENTAL CHARACTERISTICS					
WATER RESISTANCE (MATING)		PUT THE PRODUCT UNDER WATER FOR 1 min. WITH AIR PRESSURE 4.9kPa.(IP67)		NO AIR LEAKAGE	X -
COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
1	DIS-K-00000296		FS.YOSHIDA	YY.HIYAMA	16.06.02
REMARK			APPROVED	MT.SHIBUTANI	10.06.03
			CHECKED	YY.HIYAMA	10.06.03
			DESIGNED	YH.MASUZAKI	10.06.03
			DRAWN	YH.MASUZAKI	10.06.03
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-176800-01
	SPECIFICATION SHEET		PART NO.	SW20-RC1(01)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL717-5501-2-01	1/1