








Apr. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
本製品を車載用途などの高い信頼性が求められる機器にご使用の場合は、弊社までお問合せ下さい。

ELV, RoHS適合品




- 注1 推奨温度プロファイル(右表参照)
使用リフロー加熱方式
: 遠赤外線、エアータンク中または窒素
リフロー回数 : 2回
ピーク温度 : 250℃
230℃以上 : 20~40s
プリヒート温度 : 150~180℃
90~120s
- 2 手ハンダ/ハンダごて温度
: 280~300℃ 2s以内
- 3 端子平坦度は0.1mm以下。
- 4 推奨基板厚はT=1.6mmとする。
- 5 推奨はんだ厚0.15mmとする。



3	黄銅	表面: すずめっき 1μm min			
		下地: ニッケルめっき 1μm min	6	ポリエステル	
2	黄銅	表面: すずめっき 1μm min	5	ポリスチレン	
		下地: ニッケルめっき 1μm min			
1	PA	黒 UL94V-0	4	黄銅	表面: すずめっき 1μm min 下地: ニッケルめっき 1μm min
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
UNITS mm		SCALE 2:1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
		APPROVED: HK. UMEHARA	20190607	DRAWING NO.	ADC-368631-00-00
		CHECKED: HK. UMEHARA	20190607	PART NO.	ZE05-16DP-2H
		DESIGNED: YH. MAMADA	20190607	CODE NO.	CL752-2105-0-00
		DRAWN: MINTAE KANG	20190607		

梱包仕様図



Technical drawing of a reel with dimensions and labels:

- 製品向き (Product Orientation)
- エンボスキャリアテープ固定 (Embossed Carrier Tape Fixation)
- 空20個以上 (Empty 20 or more)
- 空20個以上 (Empty 20 or more)
- φ1.5 送り穴手前 (φ1.5 Feed Hole Hand Front)
- エンボスキャリアテープ固定 (Embossed Carrier Tape Fixation)
- 現品票 (Current Item Ticket)
- (61.4 : リール外側幅) (61.4 : Reel Outer Width)
- (φ 380) (φ 380)
- (φ 80) (φ 80)
- (57.4 : リール内側幅) (57.4 : Reel Inner Width)

段ボール寸法

A 3D perspective diagram of a rectangular block. The dimensions are labeled: H for height, L for length, and W for width. On the top surface, there is a small rectangular feature consisting of a small square and three parallel vertical lines.