





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



ELV, RoHS COMPLIANT



MATED CONNECTORS



RECOMMENDED PCB PATTERN



NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM

: IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
90~120s


2. TEMPERATURE FOR SOLDERING IRON
: 280~300°C WITHIN 2s

3. CO-PLANARITY SHALL BE 0.1mm MAX.

4. RECOMMENDED PCB THICKNESS IS 1.6mm.

5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.

6. : PROHIBITED PATTERN AREA





3	BRASS	SURFACE PLATING : TIN PLATING 1μm min			
		UNDER PLATING : NICKEL 1μm min			
2	BRASS	SURFACE PLATING : TIN PLATING 1μm min	6	POLYIMIDE	PICK & PLACE TAPE
		UNDER PLATING : NICKEL 1μm min	5	POLYESTER	
1	PA	BLACK UL94V-0	4	POLYSTYRENE	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-T-00006748	DESIGNED YH. MAMADA
		APPROVED : HK. UMEHARA	20181127	DRAWING NO. EDC-376503-00-00	
		CHECKED : AH. EDASHIGE	20181127	PART NO. ZE05H-4P-2V	
		DESIGNED : TY. ISHIGURO	20181127	CODE NO. CL752-2310-0-00	
		DRAWN : TY. ISHIGURO	20181127		


PACKING STYLE

REEL DIMENSION (FREE)

PACKING STYLE DRAWING



CARDBOARD DIMENSION (FREE)



W=(405) (mm)
D=(405) (mm)
H= (51) (mm)

	DRAWING NO. EDC-376503-00-00	
	PART NO. ZE05H-4P-2V	
	CODE NO. CL752-2310-0-00	 