


APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽¹⁾	
	VOLTAGE	$\triangle 2$ 60 V AC/DC	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX	
	CURRENT	2 A		(NOT DEWED)	
	APPLICABLE WIRE	AWG20~22	JACKET DIAMETER	ϕ 1.4~ ϕ 1.7mm	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING		CONFIRMED VISUALLY.		x	x
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		1A DC.	8 m Ω MAX.	x	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	8 m Ω MAX.	x	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
VIBRATION		FREQUENCY 20 TO 200Hz (88m/s ²) SWEEP TIME 3min. (ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 Ω MIN, 1 μ s MIN. ② CONTACT RESISTANCE: 16 m Ω MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
SHOCK		981m/s ² DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 Ω MIN, 1 μ s MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 16 m Ω MAX. ② INSULATION RESISTANCE:100 M Ω MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE- 40 →ROOM TEMP →125°C→ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
DRY HEAT		EXPOSED AT 140°C, 120 h.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
COLD		EXPOSED AT -40°C, 120 h.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
RESISTANCE TO SO ₂ GAS		EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	CONTACT RESISTANCE: 16 m Ω MAX.	x	—
RESISTANCE TO HIGH-PRESSURE WASHING $\triangle 2$		AFTER HEATING AT 120°C FOR 120 h, WATER AT 80°C, 10 MPa, FOR 30 sec AT THE POSITION OF ① TO ④. ROTATE THE MOUNTING BASE AT 5 r/min. 	① NO WATER PENETRATION PERMITTED. ② INSULATION RESISTANCE:100 M Ω MIN.	x	—
COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
$\triangle 2$	2	DIS-T-00005917	AN. SAIKI	HH. TSUKUMO	20200312
REMARK			APPROVED	AH. EDASHIGE	20190122
(NOTE1) "STORAGE" means a long-term storage state for the unused product.			CHECKED	HH. TSUKUMO	20190122
			DESIGNED	AS. SHIBAHARA	20190122
			DRAWN	DS. HIROWATARI	20190122
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-372039-00-00
HRS	SPECIFICATION SHEET		PART NO.	ZE064-2022SCF	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL753-2001-0-00	$\triangle 2$ 1/1