


Oct.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C <sup>(1)</sup>
	VOLTAGE	$\triangle 1$ 60 V AC/DC	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX
	CURRENT	2 A		(NOT DEWED)
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
<b>CONSTRUCTION</b>				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.		x	x
<b>ELECTRIC CHARACTERISTICS</b>				
CONTACT RESISTANCE	1A DC.	8 m $\Omega$ MAX.	-	-
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	8 m $\Omega$ MAX.	-	-
INSULATION RESISTANCE	500V DC.	100 M $\Omega$ MIN.	x	-
VOLTAGE PROOF	1000 V AC FOR 1 min.	$\triangle 1$ NO BREAKDOWN.	-	-
<b>MECHANICAL CHARACTERISTICS</b>				
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 16 m $\Omega$ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s <sup>2</sup> ) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 $\Omega$ MIN, 1 $\mu$ s MIN. ② CONTACT RESISTANCE: 16 m $\Omega$ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
SHOCK	981m/s <sup>2</sup> DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 $\Omega$ MIN, 1 $\mu$ s MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.	100N MIN.	x	-
<b>ENVIRONMENTAL CHARACTERISTICS</b>				
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 16 m $\Omega$ MAX. ② INSULATION RESISTANCE:100 M $\Omega$ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: 16 m $\Omega$ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
DRY HEAT	EXPOSED AT 140°C, 120 h.	① CONTACT RESISTANCE: 16 m $\Omega$ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
COLD	EXPOSED AT -40°C, 120 h.	① CONTACT RESISTANCE: 16 m $\Omega$ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
RESISTANCE TO SO <sub>2</sub> GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	CONTACT RESISTANCE: 16 m $\Omega$ MAX.	-	-
RESISTANCE TO HIGH-PRESSURE WASHING $\triangle 1$	AFTER HEATING AT 120°C FOR 120 h, WATER AT 80°C, 10 MPa, FOR 30 sec AT THE POSITIONS OF ① TO ④. ROTATE THE MOUNTING BASE AT 5 r/min. 	① NO WATER PENETRATION PERMITTED. ② INSULATION RESISTANCE:100 M $\Omega$ MIN.	x	-
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
$\triangle 1$ 3	DIS-T-00005917	AN. SAIKI	HH. TSUKUMO	20200312
REMARK		APPROVED	OM. MIYAMOTO	20190521
(NOTE1) "STORAGE" means a long-term storage state for the unused product.		CHECKED	HH. TSUKUMO	20190521
		DESIGNED	AS. SHIBAHARA	20190521
		DRAWN	MINTAE KANG	20190521
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-374259-00-00	
<b>HRS</b>	SPECIFICATION SHEET	PART NO.	ZE064W-24DS-HU/R (A)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL753-2005-0-00	$\triangle 1$ 1/1