



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

RoHS, ELV COMPLIANT
RoHS, ELV適合品












基板推奨寸法図
Recommended PCB layout





パネル寸法図
Pannel layout



RECOMMENDED REFLOW PROFILE

IR reflow condition	IR リフロー条件
Preheating area 150℃ for 60 to 120 seconds Peak Temperature: 250℃ Soldering area 235±5℃ or 10 seconds max. 230℃ min. for 10 30 seconds	予備加熱：150～120秒、150℃ ピーク温度：250℃ リフロー温度：235～240℃、10秒以内 230℃以上：10～30秒

Note1. The soldering process is alloed up to twice under the same condition. However, the interval between the first and second process must be maintained at the room temperature.
リフロー回数：2回。但し、2回目のリフローにおいては、一度、室温に戻すこと。

Note2. The temparature indicates the board surface temperature on the connector lead area.
リフロー温度の測定は、コネクタリード部の基板表面温度を測定のこと。

Note3. Hand soldering: 280~300℃,2s max.
手半田温度： 280～300℃、2S以内

Note4. Coplanarity: 0.1 max.
端子平坦度： 0.1以下

Note5. Recommended thickness of PCB:1.6mm
推奨基板厚：1.6mm

嵌合状態図
MATED CONNECTORS

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	BRASS	TIN PLATING			
2	PPS	LIGHT GRAY	5	PS	
1	COPPER ALLOY	TIN PLATING	4	BRASS	TIN PLATING

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△0					


HIROSE ELECTRIC CO., LTD.

APPROVED	KI. HIROKAWA	20220921	DRAWING NO. EDC-166859-58-00
CHECKED	KT. MAKI	20220921	PART NO. GT17HN-16DP-2H(58)
DESIGNED	TS. KUBOTA	20220921	CODE NO. CL0767-0153-7-58 △0 1/2
DRAWN	TS. KUBOTA	20220921	


HRS DRAWING FOR REFERENCE

FORM HC0011-5-7

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




1トレー 40個 入り 40 PCS / TRAY



製品格納状態図(2:1)
PACKAGING CONDITION

梱包仕様
W=270・D=360・H=150のサイズのダンボール箱に下図のように製品を入れる。 ダンボール箱には納入先、製品名、入り数を明記する。
PACKAGING STYLE BOX SIZE : W=270·D=360·H=150 The Delivery, a product name and a number are in the cardboard box .



HRS DRAWING FOR REFERENCE

DRAWING NO.	EDC-166859-58-00
PART NO.	GT17HN-16DP-2H(58)
CODE NO.	CL0767-0153-7-58

△0 2/2