




- Notes
- 1 Rotation example of Ref. No. ① and ② are shown.
 - 2 The tightening torque of Ref. No. ⑨: 2 to 3 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion of Ref. No. ① in order to prevent loosening.
 - 3 This product to be used with cable clamp, JR16WCC-※(72).
※ designate diameter of applicable cable.
 - 4 The cable pull and twisting strength, waterproof tightness and other characteristics may differ, depending on the cable structure, please confirm before the use.

5	Polyacetal	(White)			
4	Polyphenylene sulfide	(Black)	9	Zinc alloy	Chrome plating
3	Polyphenylene sulfide	(Black)	8	Silicone rubber	(Black)
2	Brass	Silver plating 2μm min.	7	Brass	Chrome plating
1	Zinc alloy	Chrome plating	6	Silicone rubber	(Red)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00016502	DESIGNED TY. SUZUKI
HIROSE ELECTRIC CO., LTD.		APPROVED : HY. KOBAYASHI	20230601	DRAWING NO.	EDC-111156-81-00
		CHECKED : HY. KOBAYASHI	20230601	PART NO.	RM15WTPZA-2P(81)
		DESIGNED : HT. ZENBA	20230601	CODE NO.	CL0109-1734-5-81
		DRAWN : KR. SUZUKI	20230531		
					1/1