








May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV・RoHS COMPLIANT




REFLOW TEMPERATURE PROFILE



MATED CONNECTORS




RECOMMENDED PANEL CUTOUT



RECOMMENDED PC BOARD PATTERN

- NOTE 1. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
2. REFLOW TEMPERATURE PROFILE IS AS FIGURE.
3 MICROSTRIP LINE TO BE 50Ω FOR A DIMENSION.

2	COPPER ALLOY	TIN PLATING	4	COPPER ALLOY	TIN PLATING					
1	COPPER ALLOY	TIN PLATING	3	PA	BLUE					
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS				
UNITS mm				SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : KI. HIROKAWA		20200406	DRAWING NO.		EDC-169969-55-00			
		CHECKED : MO. OKADA		20200406	PART NO.		GT21T-1P-H(C)(55)			
		DESIGNED : HK. WATANABE		20200406	CODE NO.		CL771-0067-6-55			
		DRAWN : YK. MITSUISHI		20200403			 1/			

