




May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- ① HAND CRIMPING TOOL, REF. NO. ⑩: HR10A-TC-02 (CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING: $\phi 7$
 - ② THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑥: 2 TO 2.5 N·m.
 - ③ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑨: 1.27
THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑨: 0.3 TO 0.4 N·m.
 - ④ THE TIP OF REF. NO. ⑨ SHALL BE FIXED TO THE CONCAVE PORTION WITH REF. NO. ⑩ CLAMPED TO THE CABLE.
 - ⑤ ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑥ TO REF. NO. ① IS SHOWN.
 - ⑥ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.
 - ⑦ THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0354-00.

5	BRASS	MATTE FINISH NICKEL PLATED	10	BRASS	
4	BRASS	OVER PLATING:GOLD 0.2μm min. UNDER PLATING:NICKEL 2μm min.	9	STEEL	NICKEL PLATING M2.6X0.45X3
3	BRASS		8	CHLOROPRENE RUBBER	(BLACK)
2	POLYAMIDE	(BLACK) UL94V-0	7	STEEL	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00016957	DESIGNED HT. ZENBA	CHECKED EJ. KUNII	DATE 20240227
HIROSE ELECTRIC CO., LTD.		APPROVED :MO. SATOH	20070323	DRAWING NO.	EDC3-045382-74		
		CHECKED :MO. SATOH	20070323	PART NO.	HR10A-13P-20P(74)		
		DESIGNED :TO. HORII	20070320	CODE NO.	CL0110-0713-0-74		
		DRAWN :MK. SATO	20070313				