






Nov.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 120 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽¹⁾	
	CURRENT	30 A	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX (NOT DEWED)	
	VOLTAGE	600 V AC/DC			
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x	
MARKING	CONFIRMED VISUALLY.		x	x	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	10A DC. 	50mΩ MAX.	x	-	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 10mA(DC OR 1000Hz) 	50mΩ MAX	x	-	
MECHANICAL CHARACTERISTICS					
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s ²) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② CONTACT RESISTANCE: 5mΩMAX ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 85 °C, 90 ~ 95 %, 96 h.	① INSULATION RESISTANCE:100 MΩ MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →120°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① INSULATION RESISTANCE: 100 MΩ MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
DRY HEAT	EXPOSED AT 125°C, 300 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
COLD	EXPOSED AT -40°C , 120 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	2	DIS-T-00003861	TS.SHIMIZU	AH.EDASHIGE	20180928
REMARK (NOTE1) "STORAGE" means a long-term storage state for the unused product.			APPROVED	HK.UMEHARA	20171129
			CHECKED	HK.UMEHARA	20171129
			DESIGNED	KO.NAKAMURA	20171129
			DRAWN	MN.SATOH	20171129
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-368757-00-00	
	SPECIFICATION SHEET		PART NO.	HVH-280-4.2CF	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL778-0503-0-00	 1/1