

APPLICABLE STANDARD		UL approved (E52653).			
RATING	OPERATING TEMPERATURE RANGE	-25℃ TO +85℃	STORAGE TEMPERATURE RANGE	-10℃ TO +60℃	
	VOLTAGE	AC 60 V , DC 60 V	WIRE SIZE	AWG #26 MAX (NO. 1, 3, 4, 6) AWG #20 MAX (NO. 2, 5)	
	CURRENT	1 A (NO. 1, 3, 4, 6) 4 A (NO. 2, 5)	APPLICABLE CABLE	φ5±0.2	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A	15 mΩ MAX.	X	X
INSULATION RESISTANCE		100 V DC.	1000 MΩ MIN.	X	X
VOLTAGE PROOF		300 V AC. FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X
MECHANICAL CHARACTERISTICS					
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.	INSERTION AND WITHDRAWAL FORCES LOCKING DEVICE WITH UNLOCK : 25 N MAX.	X	—
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.	CONTACT RESISTANCE: 30 mΩ MAX.	X	—
VIBRATION		FREQUENCY: 10 → 55 → 10 (Hz) (1CYC, 5min), SINGLE AMPLITUDE 0.75 mm, AT 10 CYC, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—
SHOCK		IN OPPOSITE DIRECTIONS OF EACH 3 DIMENSION AXIS FOR 3 TIMES AT 490 m/s ² DURATIONS OF PULSE 11 ms.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—
BREAKING STRENGTH		MAX 100 N SHALL BE APPLIED TO CABLE IN UP AND DOWN, LEFT AND RIGHT DIRECTIONS WHEN MATED.	NO BREAKAGE MAX 100N.	X	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 10 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 100 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → R/T ⁽¹⁾ → +85 → R/T °C TIME 30 → 2 TO 3 → 30 → 2 TO 3 min UNDER 5 CYCLES.	① INSULATION RESISTANCE: 100 MΩ MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO MAJOR CORROSION DAMAGE TO ELECTRICAL AND MECHANICAL FUNCTIONS (INTERMATEABILITY).	X	—
DRY HEAT		EXPOSED AT +85 °C, 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
COLD		EXPOSED AT -55 °C, 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, +350±10℃, FOR IMMERSION DURATION, 5±1 s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, +350±10℃ FOR IMMERSION DURATION, 2 TO 3 s.	SOLDER SURFACE TO BE FREE FROM PIN-HOLE, NO WETTING AND OTHER DEFECTS.	X	—
SEALING (MATING SIDE) ⁽²⁾		EXPOSED AT A DEPTH OF 1.8 m FOR 48 h.	NO WATER PENETRATION INSIDE CONNECTOR.	X	—
AIR TIGHTNESS (MATING SIDE) ⁽²⁾		APPLY AIR PRESSURE 17.6kPa FOR 0.5min TO INSIDE CONNECTOR.	NO AIR BUBBLES INSIDE CONNECTOR.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK			APPROVED	HY. KOBAYASHI	18.03.15
NOTES(1)R/T : ROOM TEMPERATURE			CHECKED	HY. KOBAYASHI	18.03.15
(2)SEALING AND AIRTIGHTNESS SHALL BE TESTED BY APPLICABLE CONNECTOR.			DESIGNED	TY. SUZUKI	18.03.15
Unless otherwise specified, refer to IEC 60512.(JIS C 5402)			DRAWN	TY. SUZUKI	18.03.15
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-119201-31-00	
HRS	SPECIFICATION SHEET		PART NO.	LF07WBP-6P-A (31)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL136-0016-0-31	△ 1/1