

Apr.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Operating condition	Storage temperature range (before unpacking)	-10 to +60 [deg. C] (40 to 75%RH)	Storage temperature range (after mounting, but not operating)	-40 to +85 [deg. C] (85%RH MAX) No freezing and condensing
	Operating temperature range	-10 to +60 [deg. C] (85%RH MAX) No freezing and condensing	Characteristic impedance	Differential 100 [ohm]
	Input signal IF	SLVS-200	ACTIVATE voltage	1.0 to 3.6V
	Input signal voltage	Differential voltage 200 to 1400 mVp	Input power voltage	3.0 to 3.6V (typ 3.3V)
	Suitable connector	(BF4-IR2) BF4-IR2-16P-0.5SH,		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
Dimension, Construction and Finishing	Check visually and measure dimension with dimension measurement instrument.	According to the drawing	X	X
Marking	Check visually.		X	X

ELECTRIC CHARACTERISTICS				
Data rate performance	Measure eye diagram when input differential 200mVp signal.	No mask hit at 0.05 to 6.25 Gbps (The mask should be similar to standard ethernet mask)	X	-
	Measure eye diagram input 6.25Gbps PRBS7 differential 200mVp signal.	No mask hit (The mask should be similar to standard ethernet mask)	X	X
Signal detect (OE-SDn)	Shall be turned OE-SDn=Low when EO-ACT=High and VDD=3.3V. (Same measurement method as "Data rate")	OE-SDn voltage -0.3 to 1.0V	X	X
ACT detect (EO-ACTn)	Shall be turned EO-ACTn=Low when TX is during VDD=3.3V.	EO-ACTn voltage -0.3 to 1.0V	X	X
Bit error rate (BER)	Measure BER with BERT during input differential 6.25Gbps PRBS7 200mVp signal.	$< 1 \times 10^{-12}$	X	-
Power consumption	Measure current by digital multimeter during operating condition at VDD=3.3V.	$\leq 160\text{mW}$	X	-
Output signal voltage	Shall be checked by eye diagram when input 6.25Gbps PRBS7 differential 200mVp signal.	160 to 330mVp	X	X

OPTICAL CHARACTERISTICS				
LED light emission (Green)	Apply V=3.0 to 3.6V at the pin, then check if LED light is visible or not.	Green light shall be visible	X	X
LED light emission (Amber)	Apply V=3.0 to 3.6V at the pin, then check if LED light is visible or not.	Amber light shall be visible	X	X

MECHANICAL CHARACTERISTICS				
Mating Durability	(BF4-IR2) 1000 cycles of mating and unmating with BF4-IR2 socket.	No looseness, breakage and cracks (Visual and data transmission check before and after test)	X	-
			X	-
Vibration	Vibration for 2 hours in 3 directions, at an amplitude of 1.5mm with the frequency range 10 to 55 [Hz].		X	-
Shock	3 times and 3 directions with the acceleration 490 [m/s ²] in duration 11ms.		X	-
Fiber clamping strength	Loading tensile force to the fiber until break for same direction with fiber exit.	> 10N	X	-


COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0				

REMARK Each test item shall be checked by mating with suitable receptacle connector on evaluation board (BF4-IR2) This specifications sheet is based on using BF4MC type in BF4-IR2.	APPROVED	YY.HIYAMA	20221212
	CHECKED	TS.YAMAZAKI	20221208
	DESIGNED	SK.AOYAMA	20221206
	DRAWN	SK.AOYAMA	20221206

Note QT:Qualification Test, AT:Assurance Test	DRAWING NO.	ELC-392025-00-00
---	-------------	------------------

HRS	SPECIFICATION SHEET	PART NO.	BF4-IR2IR2-01-5M	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0831-1277-0-00	△ 1/2

Apr.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
ENVIRONMENTAL CHARACTERISTICS				
Transportation and storage temperature and humidity test	Applying temperature and humidity load as below Testmethod Start at 23 deg.C⇒-20 deg.C (72hours) ⇒ (Ramp up time 1.5hours) ⇒23 deg.C⇒ (Ramp down time 1.2hours) ⇒ +60 deg.C, 90%Rh (72hours) ⇒23 deg.C	No looseness, breakage and cracks (Visual and data transmission check before test, intermediate test and after test)	X	-
Temperature cycling test	-40 to 85 degree Celsius with dwell time of 10min, 100 cycles		X	-
High temperature storage	85 degree Celsius , 1000 hours		X	-
Low temperature storage	-40 degree Celsius, 1000 hours		X	-
Temperature and Humidity cycling	Temperature, Humidity: -10 ⇔ 65 degree Celsius, 93%RH w/o applying current. Number of cycle: 10 cycles, Cycle time: 24 hours/cycle 		X	-
ESD tolerance	(BF4-IR2) Applied voltage 2kV (Human Body Model)		X	-
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-392025-00-00	
HRS	SPECIFICATION SHEET	PART NO.	BF4-IR2IR2-01-5M	
	HIROSE ELECTRIC CO., LTD.	CODE NO	CL0831-1277-0-00	△ 2/2