




Apr.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



PACKING REEL (FREE)



- NOTES
1. APPLICABLE WIRE IS AWG #16~#18.
 INSULATION DIAMETER ϕ 2.25mm MAX.
 WHEN CRIMPING AWG#16 (UL1007 ϕ 2.50mm),
 DUE TO THE DESIGN OF INSULATION BARREL,
 THE SHAPE OF CRIMP DOES NOT COVER INSULATION.
 IT DOES NOT AFFECT THE PRODUCT QUALITY.
 INCORRECT CRIMPING MAY INTERFERE CONTACT INSERTION TO THE HOUSING.
 REFER TO THE CRIMPING QUALITY STANDARD, ATAD-E3238 FOR THE DETAILS.
 2. PER REEL : 6000 CONTACTS.
 3. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
 WILL BE SPECIFIED ACCORDING TO AWG# OR WIRE APPLIED.
 4. REFER TO ETAD-E2961 FOR INCORPORABLE CONNECTOR PARTS AND APPLICABLE CONNECTOR.

NO.		MATERIAL		FINISH . REMARKS		NO.		MATERIAL		FINISH . REMARKS	
		1		COPPER ALLOY				CONTACT AREA : GOLD PLATING 0.2 μ m min		TERMINAL AREA : TIN PLATING 1 μ m min	
								UNDER : NICKEL PLATING 0.5 μ m min			
UNITS		SCALE		COUNT		DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	
mm		5 : 1		\triangle		DIS-A-00063387				DATE	
HIROSE ELECTRIC CO., LTD.		APPROVED : MN. KENJO		20211224		DRAWING NO.		EDC-397341-00-00			
		CHECKED : KG. OKITA		20211224		PART NO.		PQ50S2-1618SCFA			
		DESIGNED : HY. MATSUDA		20211224		CODE NO.		CL0236-0042-0-00			
		DRAWN : YK. MORIYAMA		20211224							