


May.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- △△ NOTES
1. APPLICABLE WIRE IS AWG #14~#15.
INSULATION DIAMETER φ 3.30mm MAX.
WHEN CRIMPING AWG#14 (UL1015 φ 3.80mm),
DUE TO THE DESIGN OF INSULATION BARREL,
THE SHAPE OF CRIMP DOES NOT COVER INSULATION.
IT DOES NOT AFFECT THE PRODUCT QUALITY.
INCORRECT CRIMPING MAY INTERFERE CONTACT INSERTION TO THE HOUSING.
REFER TO THE CRIMPING QUALITY STANDARD,ATAI-E2926 FOR THE DETAILS.
 2. PER REEL : 3500 CONTACTS.
 3. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
(CRIMP HEIGHT etc.) WILL BE SPECIFIED ACCORDING TO
AWG # OR WIRE APPLIED.

PACKING REEL (FREE)

NO. 1		MATERIAL COPPER ALLOY		CONTACT AREA : GOLD PLATING 0.2μm MIN. TERMINAL AREA : TIN PLATING 1μm MIN. UNDER PLATING : NICKEL PLATING 0.5μm MIN.	
UNITS	mm	SCALE	5 : 1	COUNT	1
DESCRIPTION OF REVISIONS			DESIGNED	CHECKED	
DIS-E-004877			TY. MIURA	AH. KODAMA	
DATE			DATE		
13.06.24			13.12.20		
APPROVED : RI. TAKAYASU		13.06.24		DRAWING NO. EDC3-128311-00	
CHECKED : AH. KODAMA		13.06.24		PART NO. PQ50A-15PCFA	
DESIGNED : YH. MAMADA		13.06.21		CODE NO. CL236-2073-1-00	
DRAWN : YH. MAMADA		13.06.21		1/1	