

1		2		3		4																																														
<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~044*1TS~</td><td>WHITE</td></tr><tr><td>~044*2TS~</td><td>BLACK</td></tr></tbody></table>								Part No.	Cable color	~044*1TS~	WHITE	~044*2TS~	BLACK																																							
Part No.	Cable color																																																			
~044*1TS~	WHITE																																																			
~044*2TS~	BLACK																																																			
NOTE 1. Please place an order as the assembled product. 2. There is no compatibility between W.FL series and W.FL2 series. 3 The drawing shows mated connector height only. 4 We indicate the length of the harness on the last of product name, 'L' part. 5 Tolerance for [L] <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 200</td><td>±4</td></tr><tr><td>200 < L ≤ 500</td><td>±8</td></tr><tr><td>500 < L ≤ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table> 6 Connector rotation angle is within ±45 degree from the above image. For long length in the case of L>150, the angle is optional. 7. Specifications are subject to change without notice.								Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 200	±4	200 < L ≤ 500	±8	500 < L ≤ 1000	±12	1000 < L	±1.5%																																			
Length L [mm]	Tolerance [mm]																																																			
35 ≤ L ≤ 200	±4																																																			
200 < L ≤ 500	±8																																																			
500 < L ≤ 1000	±12																																																			
1000 < L	±1.5%																																																			
【 DIMENSIONS OF CONNECTOR 】																																																				
【 PRECAUTIONS FOR HANDLING 】 ◆ Connector insertion and extraction a. Insert the connector as perpendicularly to the mating surface as possible with aligning the mating axes of both connectors by specialised insertion JIG. Part No. :W.FL-LP-IN<CL331-0323-2> or W.FL2-LP-IN.OUT<CL331-0321-7> Do not excessively slant the connectors when inserting. b. Connector shall be extracted by specialised extraction JIG. Part No. :W.FL2-LP-IN.OUT Never hold the cable when extracting the Cable because it damages the connector. ◆ Allowable loads on the cable after the connectors are mated. The right figures show the maximum allowable loads on the cable. Do not apply loads exceeding these values to the cable.																																																				
<table border="1"><thead><tr><th>1</th><th>W.FL2-LP-040HF(06)</th><th>CL331-0311-3-06</th><th>2</th><th>0.64 Dia. coaxial cable</th></tr><tr><th>No.</th><th>Part No.</th><th>Code No.</th><th>No.</th><th>Part No.</th></tr></thead><tbody><tr><td colspan="5">UNITS mm</td></tr><tr><td colspan="5">SCALE FREE</td></tr><tr><td colspan="5">COUNT</td></tr><tr><td colspan="5">DESCRIPTION OF REVISIONS</td></tr><tr><td colspan="5">DESIGNED</td></tr><tr><td colspan="5">CHECKED</td></tr><tr><td colspan="5">DATE</td></tr></tbody></table>								1	W.FL2-LP-040HF(06)	CL331-0311-3-06	2	0.64 Dia. coaxial cable	No.	Part No.	Code No.	No.	Part No.	UNITS mm					SCALE FREE					COUNT					DESCRIPTION OF REVISIONS					DESIGNED					CHECKED					DATE				
1	W.FL2-LP-040HF(06)	CL331-0311-3-06	2	0.64 Dia. coaxial cable																																																
No.	Part No.	Code No.	No.	Part No.																																																
UNITS mm																																																				
SCALE FREE																																																				
COUNT																																																				
DESCRIPTION OF REVISIONS																																																				
DESIGNED																																																				
CHECKED																																																				
DATE																																																				
<table border="1"><thead><tr><th colspan="2">APPROVED :NK. NINOMIYA</th><th colspan="2">20190717</th><th colspan="2">DRAWING NO.</th></tr><tr><th colspan="2">CHECKED :NK. NINOMIYA</th><th colspan="2">20190717</th><th colspan="2">PART NO.</th></tr><tr><th colspan="2">DESIGNED :MK. INOUE</th><th colspan="2">20190717</th><th colspan="2">CODE NO.</th></tr><tr><th colspan="2">DRAWN :MK. INOUE</th><th colspan="2">20190717</th><th colspan="2">NO.</th></tr></thead><tbody><tr><td colspan="4">WFL2-2HF6-044**TS-A-L</td><td colspan="2">4</td></tr><tr><td colspan="4"></td><td colspan="2">1/1</td></tr></tbody></table>								APPROVED :NK. NINOMIYA		20190717		DRAWING NO.		CHECKED :NK. NINOMIYA		20190717		PART NO.		DESIGNED :MK. INOUE		20190717		CODE NO.		DRAWN :MK. INOUE		20190717		NO.		WFL2-2HF6-044**TS-A-L				4						1/1										
APPROVED :NK. NINOMIYA		20190717		DRAWING NO.																																																
CHECKED :NK. NINOMIYA		20190717		PART NO.																																																
DESIGNED :MK. INOUE		20190717		CODE NO.																																																
DRAWN :MK. INOUE		20190717		NO.																																																
WFL2-2HF6-044**TS-A-L				4																																																
				1/1																																																

FORM HC0011-5-51