


Oct.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS DRAWING FOR REFERENCE

- △△ NOTES
1. APPLICABLE WIRE IS AWG #14~#15.
 INSULATION DIAMETER $\phi 3.30$ mm MAX.
 WHEN CRIMPING AWG#14 (UL1015 $\phi 3.80$ mm),
 DUE TO THE DESIGN OF INSULATION BARREL,
 THE SHAPE OF CRIMP DOES NOT COVER INSULATION.
 IT DOES NOT AFFECT THE PRODUCT QUALITY.
 REFER TO ATAI-E2926 FOR CRIMP QUALITY STANDARDS.
 2. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
 (CRIMP HEIGHT etc.) WILL BE SPECIFIED ACCORDING TO
 AWG # OR WIRE APPLIED.
 3. ONE PACKAGE CONSISTS OF 100 PCS.

NO. 1		MATERIAL COPPER ALLOY		FINISH . REMARKS CONTACT AREA : GOLD PLATING 0.2μm MIN. TERMINAL AREA : TIN PLATING 1μm MIN. UNDER PLATING : NICKEL PLATING 0.5μm MIN.		
UNITS mm	SCALE 5 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-E-004877	DESIGNED TY. MIURA	CHECKED AH. KODAMA	DATE 13. 12. 20
APPROVED : RI. TAKAYASU 13. 06. 24		DRAWING NO. EDC3-128348-00				
CHECKED : AH. KODAMA 13. 06. 24		PART NO. PQ50A-15PCA				
DESIGNED : YH. MAMADA 13. 06. 21		CODE NO. CL236-2075-7-00				
DRAWN : YH. MAMADA 13. 06. 21						