

Applicable standard					
Rating	Operating temperature range	-40 °C to +90 °C(90 %RH Max.)	Storage temperature range	-40 °C to +90 °C(90 %RH Max.)	
	Power	-- W	Characteristic impedance	50 Ω(0 to 8 GHz) $\triangle 1$	
	Peculiarity	----	Applicable cable	F-MF103CN (Nissei Electric Co., Ltd.)	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
General examination		Visually and by measuring instrument.	According to drawing.	X	X
ELECTRICAL CHARACTERISTICS					
Contact resistance	10 mA Max.(DC or 1000 Hz)	Center contact 1.4(Lmax+1.1)+24 mΩ Max.	X	X	
		Outer contact 0.3(Lmax+1.1)+14 mΩ Max.	X	X	
Insulation resistance	100 V DC.	500 MΩ Min.	X	X	
Withstanding voltage	200 V AC for 1 min. current leakage 2 mA Max.	No breakdown.	X	X	
Voltage standing wave ratio $\triangle 1$	Frequency 0 to 3 GHz.	VSWR 1.3 Max.	X	-	
	Frequency 3 to 6 GHz.	VSWR 1.35 Max.			
	Frequency 6 to 8 GHz.	VSWR 1.4 Max.			
Insertion loss	Frequency - to - GHz.	--- dB Max.	-	-	
MECHANICAL CHARACTERISTICS					
Cable clamp strength (Against cable pull)	Using a pulling tester, pull the cable axially at a rate of 10 mm/min. and record the strength at which the cable or connector breaks.		7 N Min.	X	-
	Count	Description of revisions	Designed	Checked	Date
$\triangle 1$	2	DIS-D-00013741	MS. MATSUMOTO	MT. KANEKO	20221108
Remark Notes 1. "L" at the end of the product name indicates the cable length (unit:mm). 2. Specifications are subject to change without notice. Unless otherwise specified, refer to IEC 60512.			Approved	TS.NAKAGAWA	20221012
			Checked	MT.KANEKO	20221011
			Designed	MS.MATSUMOTO	20221011
			Drawn	MS.MATSUMOTO	20221011
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		Drawing No.			
	SPECIFICATION SHEET		Part No.	SRWBPJ-UHF6-04N*TV-AL	
	HIROSE ELECTRIC CO., LTD.		Code No.	$\triangle 1$	1/1