

Oct.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE

APPLICABLE STANDARD

RATING	OPERATING TEMPERATURE RANGE	-55℃ TO +85℃(note1)	STORAGE TEMPERATURE RANGE	-10℃ TO +60℃
	VOLTAGE	30 V AC/DC	APPLICABLE CONNECTOR	BK13C06-60DP/2-0.35V(**)
	CURRENT	SIGNAL CONTACT 0.3A(note2) POWER CONTACT 5.0A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION

GENERAL EXAMINATION	CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRICAL CHARACTERISTICS


CONTACT RESISTANCE	20mV AC OR LESS 1kHz, 1mA	SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX	X	-
INSULATION RESISTANCE	100V DC	50MΩ MIN	X	-
VOLTAGE PROOF	100V AC FOR 1min.	NO FLASHOVER OR BREAKDOWN	X	-

MECHANICAL CHARACTERISTICS

MECHANICAL OPERATION	10 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.	X	-
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK	490 m/s ² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-

ENVIRONMENTAL CHARACTERISTICS

RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)	① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2℃, 90 TO 95%, 96h.	① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SULPHUR DIOXIDE	EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)	① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-

REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT. Note 2 : MAX 12A AT TOTAL PIN CONTACTS.	H.K.JEON	H.K.JEON	H.W.JO	H.W.JO	
Unless otherwise specified, refer to JIS C 5402 and IEC 60512	20.02.19	20.02.19	20.02.19	20.02.19	

Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST

HIROSE KOREA CO.,LTD.	SPECIFICATION SHEET	PART NO. BK13C06-60DS/2-0.35V(800)
CODE NO.(OLD)	DRAWING NO. ELC3-632999-80	CODE NO. CL 6665-0030-6-800
		1/1