















	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
	10	RE-6-2403	LCE	JHW	21.09.13					
	2	RE-6-2541	LCE	JHW	21.12.27					
APPLICABLE STANDARD										
RATING	OPERATING TEMPERATURE RANGE		-55℃ TO +85℃(note1)			STORAGE TEMPERATURE RANGE		-10℃ TO +60℃		
	VOLTAGE		 60 V AC/DC			APPLICABLE CONNECTOR		BK22C07-4DP/2-0.4V(***)		
	CURRENT		SIGNAL CONTACT 0.3A POWER CONTACT 15.0A							
SPECIFICATIONS										
ITEM		TEST METHOD				REQUIREMENTS			QT	AT
CONSTRUCTION										
GENERAL EXAMINATION		CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.			X	X
MARKING		CONFIRMED VISUALLY.							X	X
ELECTRICAL CHARACTERISTICS										
CONTACT RESISTANCE		20mV AC OR LESS 1kHz, 1mA				SIGNAL CONTACT : 30mΩ MAX  POWER CONTACT : 5mΩ MAX 			X	-
INSULATION RESISTANCE		100V DC				50MΩ MIN			X	-
VOLTAGE PROOF		150V AC FOR 1min. 				NO FLASHOVER OR BREAKDOWN			X	-
MECHANICAL CHARACTERISTICS										
MECHANICAL OPERATION		10 TIMES INSERTIONS AND EXTRACTIONS.				① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX  POWER CONTACT : 5mΩ MAX  ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.			X	-
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
SHOCK		490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
ENVIRONMENTAL CHARACTERISTICS										
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)				① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX  POWER CONTACT : 5mΩ MAX  ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2℃, 90 TO 95%, 96h.				① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX  POWER CONTACT : 5mΩ MAX  ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)				① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX  POWER CONTACT : 5mΩ MAX  ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
REMARKS Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT.					DRAWN D.K.YUN	DESIGNED D.K.YUN	CHECKED S.Sunaga	APPROVED H.W.JO	RELEASED	
Unless otherwise specified, refer to JIS C 5402 and IEC 60512					20.12.29	20.12.29	20.12.29	20.12.29		
Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST										
HIROSE KOREA CO.,LTD.			SPECIFICATION SHEET				PART NO. BK22C07-4DS/2-0.4V(800)			
CODE NO.(OLD)			DRAWING NO. ELC3-6333242-08			CODE NO. CL 6677-0002-0-800			1/1	