	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△1	12	RE-6-2247	JHK	JHW	21.04.20					
△2	2	RE-6-2541	JHK	JHW	21.12.27					

APPLICABLE STANDARD

RATING	OPERATING TEMPERATURE RANGE	−55℃ TO +85℃(note1)	STORAGE TEMPERATURE RANGE	−10℃ TO +60℃
	VOLTAGE	△2 60 V AC/DC	APPLICABLE CONNECTOR	BK22C07-6DS/2-0.4V(***)
	CURRENT	SIGNAL CONTACT 0.3A POWER CONTACT 15.0A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRICAL CHARACTERISTICS				
CONTACT RESISTANCE	20mV AC OR LESS 1kHz, 1mA	SIGNAL CONTACT : 30mΩ MAX △1 POWER CONTACT : 5mΩ MAX △1	X	−
INSULATION RESISTANCE	100V DC	50MΩ MIN	X	−
VOLTAGE PROOF	150V AC FOR 1min. △2	NO FLASHOVER OR BREAKDOWN	X	−
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	10 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX △1 POWER CONTACT : 5mΩ MAX △1 ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.	X	−
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	−
SHOCK	490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	−
ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE −55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX △1 POWER CONTACT : 5mΩ MAX △1 ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	−
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2℃, 90 TO 95%, 96h.	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX △1 POWER CONTACT : 5mΩ MAX △1 ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	−
SULPHUR DIOXIDE	EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX △1 POWER CONTACT : 5mΩ MAX △1 ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	−

REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT.	D.K.YUN	D.K.YUN	S.Sunaga	H.W.JO	
Unless otherwise specified, refer to JIS C 5402 and IEC 60512	20.12.29	20.12.29	20.12.29	20.12.29	

Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST

HIROSE KOREA CO.,LTD.	SPECIFICATION SHEET	PART NO. BK22C07-6DP/2-0.4V(800)

CODE NO.(OLD)	DRAWING NO.	CODE NO.	
	△1 ELC4-633344-80	△1 CL 6677-0003-3-800	1/1

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.