


Jun. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
<b>APPLICABLE STANDARD</b>									
RATING	OPERATING TEMPERATURE RANGE	-55°C TO +85°C(note1)			STORAGE TEMPERATURE RANGE	-10°C TO +60°C			
	VOLTAGE	30 V AC/DC			APPLICABLE CONNECTOR	BK10C05-50DS/2-0.3V(**)			
	CURRENT	SIGNAL CONTACT 0.3A(note2) POWER CONTACT 5.0A							
<b>SPECIFICATIONS</b>									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
<b>CONSTRUCTION</b>									
GENERAL EXAMINATION		CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			X	X
MARKING		CONFIRMED VISUALLY.						X	X
<b>ELECTRICAL CHARACTERISTICS</b>									
CONTACT RESISTANCE		20mV AC OR LESS 1kHz, 1mA			SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 30mΩ MAX			X	-
INSULATION RESISTANCE		100V DC			50MΩ MIN			X	-
VOLTAGE PROOF		100V AC FOR 1min.			NO FLASHOVER OR BREAKDOWN			X	-
<b>MECHANICAL CHARACTERISTICS</b>									
MECHANICAL OPERATION		10 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 50mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.			X	-
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
SHOCK		490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
<b>ENVIRONMENTAL CHARACTERISTICS</b>									
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85°C TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)			① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 50mΩ MAX ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2°C, 90 TO 95%, 96h.			① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 50mΩ MAX ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h, 25°C, 75±5%RH. (Test standard : JIS C 60068)			① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 50mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
<b>REFERENCE DRAWING</b>									
REMARKS Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT. Note 2 : MAX 12A AT TOTAL PIN CONTACTS. Unless otherwise specified, refer to JIS C 5402 and IEC 60512				DRAWN D.W.JEONG 24.01.19	DESIGNED D.W.JEONG 24.01.19	CHECKED Y.J.LEE 24.01.19	APPROVED H.W.JO 24.01.19	RELEASED 	
Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST									
HIROSE KOREA CO.,LTD.				SPECIFICATION SHEET			PART NO. BK10C05-50DP/2-0.3V(895)		
CODE NO.(OLD) CL		DRAWING NO. ELC4-633583-95			CODE NO. CL 6666-0063-1-895			1 1	