

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾			STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾			
	VOLTAGE	125 V AC			OPERATING HUMIDITY RANGE	40 % TO 80 %			
	CURRENT	0.5 A			STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾			
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			×	×
MARKING		CONFIRMED VISUALLY.						×	×
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).			45 mΩ MAX.			×	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, 1 mA(DC OR 1000Hz)			55 mΩ MAX.			×	
INSULATION RESISTANCE		250 V DC.			100 MΩ MIN.			×	
VOLTAGE PROOF		300 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.			×	
MECHANICAL CHARACTERISTICS									
MECHANICAL OPERATION		500 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 55 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			×	
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.52 mm, AT 2 h FOR 3 DIRECTION.			① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			×	
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.						×	
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.			① CONTACT RESISTANCE: 55 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN.			×	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE: -55→+15→+35→+85→+15→+35°C TIME 30 → 10~15 → 30 → 10~15 min UNDER 5 CYCLES.			③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			×	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			① CONTACT RESISTANCE: 55 mΩ MAX. ② NO HEAVY CORROSION.			×	
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA-38)						×	
RESISTANCE TO SOLDERING HEAT		1) SOLDER BATH: SOLDER TEMPERATURE, 260±5°C FOR IMMERSION, DURATION, 10±1s. 2) SOLDERING IRONS : 360°C FOR 5 s.			NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.			×	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE 240±3°C FOR IMMERSION DURATION, 2s.			A NEW UNIFORM COATING OF SOLDER SHALL OVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.			×	
REMARKS									
1) TEMPERATURE RISE INCLUDED WHEN ENERGIZED. 2) THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
					I. OKAYAMA	K. NAKAMURA	H. Okawa	H. Okawa	
Unless otherwise specified, refer to MIL-STD-1344.					04.06.09	04.06.09	04.06.09	04.06.09	
Note QT: Qualification Test AT: Assurance Test ×: Applicable Test									
HS HIROSE ELECTRIC CO., LTD.					SPECIFICATION SHEET				
CODE NO.(OLD)					PART NO.				
CL					FX2C2-**P-1. 27DSAL (71)				
DRAWING NO.					CODE NO.				
ELC4 - 083050-21					CL 572				
					1/1				