






May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
本製品を車載用途などの高い信頼性が求められる機器にご使用の場合は、弊社までお問合せ下さい。




- 注 1 ロックは2～3極が中央に1つ、4極以上が図面通り2つ設ける。
2 DF13-*S-1.25Cとのカン合高さは、5.3mm。
3 推奨スルーホール径：φ0.6±0.03
4 1バック100個梱包。




製品名	製品コード	極数	A	B	C
DF13- 2P-1.25DSA(05)	CL536-0101-9-05	2	1.25	3.15	4.15
DF13- 3P-1.25DSA(05)	CL536-0102-1-05	3	2.5	4.4	5.4
DF13- 4P-1.25DSA(05)	CL536-0103-4-05	4	3.75	5.65	6.65
DF13- 5P-1.25DSA(05)	CL536-0104-7-05	5	5	6.9	7.9
DF13- 6P-1.25DSA(05)	CL536-0105-0-05	6	6.25	8.15	9.15
DF13- 7P-1.25DSA(05)	CL536-0106-2-05	7	7.5	9.4	10.4
DF13- 8P-1.25DSA(05)	CL536-0107-5-05	8	8.75	10.65	11.65
DF13- 9P-1.25DSA(05)	CL536-0108-8-05	9	10	11.9	12.9
DF13-10P-1.25DSA(05)	CL536-0109-0-05	10	11.25	13.15	14.15
DF13-11P-1.25DSA(05)	CL536-0110-0-05	11	12.5	14.4	15.4
DF13-12P-1.25DSA(05)	CL536-0111-2-05	12	13.75	15.65	16.65
DF13-13P-1.25DSA(05)	CL536-0112-5-05	13	15	16.9	17.9
DF13-14P-1.25DSA(05)	CL536-0113-8-05	14	16.25	18.15	19.15
DF13-15P-1.25DSA(05)	CL536-0114-0-05	15	17.5	19.4	20.4


2 ソケットかん合図



3 推奨基板パターン図

(推奨基板厚 t=1.0mm)



1			ポリアミド樹脂		BEIGE(NATURAL)・UL94V-0		2		黄銅		表面:すずめっき 1μm min 下地:銅めっき 1μm min								
NO.		MATERIAL		FINISH , REMARKS			NO.		MATERIAL		FINISH , REMARKS								
UNITS mm				SCALE 5 : 1				COUNT		DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE			
 HIROSE ELECTRIC CO., LTD.				APPROVED :SJ. OKAMURA				20211217				DRAWING NO.				ADC-083673-05-00			
				CHECKED :SZ. ONO				20211217				PART NO.				DF13-*P-1.25DSA(05)			
				DESIGNED :HT. SATO				20211217				CODE NO.				CL536-			
				DRAWN :SK. CHIBA				20211217				 1/1							