





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




- NOTES 1. The dimension in parentheses are for reference.  
2. Lead CO-PLANARITY shall be 0.1 MAX.  
3. See dimension table in the appendix.  
4. This product satisfies halogen free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1500ppm maximum total of chlorine and bromine.  
5. 'n' represents the number of contacts.  
6. See dimension table in the appendix.


|                           |                 |                                                                                                  |           |                          |                             |
|---------------------------|-----------------|--------------------------------------------------------------------------------------------------|-----------|--------------------------|-----------------------------|
| 4                         | PHOSPHOR BRONZE | (CONTACT AREA: LEAD)<br>GOLD PLATING 0.05μm MIN. OVER NICKEL 1μm MIN.<br>(OTHER) NICKEL 1μm MIN. |           |                          |                             |
| 3                         | PHOSPHOR BRONZE | (CONTACT AREA: LEAD)<br>GOLD PLATING 0.05μm MIN. OVER NICKEL 1μm MIN.<br>(OTHER) NICKEL 1μm MIN. | 8         | (CONNECTOR)              |                             |
| 2                         | LCP             | (BLACK)                                                                                          | 7         | POLYSTYRENE              |                             |
| 1                         | LCP             | (BEIGE)                                                                                          | 6         | POLYESTER                |                             |
|                           |                 |                                                                                                  | 5         | POLYSTYRENE              |                             |
| NO.                       | MATERIAL        | FINISH . REMARKS                                                                                 | NO.       | MATERIAL                 | FINISH . REMARKS            |
| UNITS<br>mm               |                 | SCALE<br>5 : 1                                                                                   | COUNT<br> | DESCRIPTION OF REVISIONS | DESIGNED<br>CHECKED<br>DATE |
| HIROSE ELECTRIC CO., LTD. |                 | APPROVED : NF. MIYAZAKI                                                                          | 16.10.28  | DRAWING NO.              | EDC-349783-00-00            |
|                           |                 | CHECKED : YH. MICHIDA                                                                            | 16.10.28  | PART NO.                 | FH40-**S-0.5SV(99)          |
|                           |                 | DESIGNED : RT. IKEDA                                                                             | 16.10.28  | CODE NO.                 | CL580                       |
|                           |                 | DRAWN : RK. OGASAWARA                                                                            | 16.10.28  |                          |                             |

## RECOMMENDED PCB MOUNTING PATTERN

NUMBER OF CONTACTS: EVEN NUMBER




NUMBER OF CONTACTS: ODD NUMBER




## RECOMMENDED STENCIL PATTERN (RECOMMENDED STENCIL THICKNESS : t=0.15)

NUMBER OF CONTACTS: EVEN NUMBER





NUMBER OF CONTACTS: ODD NUMBER



**HRS**

|             |                    |
|-------------|--------------------|
| DRAWING NO. | EDC-349783-00-00   |
| PART NO.    | FH40-**S-0.5SV<99> |
| CODE NO.    | CL580              |





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

| PART NO.           | CODE NO.        | NUMBER OF CONTACT | DIMENSION OF CONNECTOR, PCB MOUNTING PATTERN, STENCIL PATTERN AND FFC/FPC |      |      |      |      | DIMENSION OF DRAWING FOR PACKING |      |      |      |      |      |      |
|--------------------|-----------------|-------------------|---------------------------------------------------------------------------|------|------|------|------|----------------------------------|------|------|------|------|------|------|
|                    |                 |                   | A                                                                         | B    | C    | D    | E    | F                                | G    | H    | J    | K    | L    | M    |
| FH40-10S-0.5SV(99) | CL580-2104-6-99 | 10                | 5.57                                                                      | 8.2  | 4.5  | 5.5  | 7.1  | 16                               | —    | 7.5  | 8.4  | 5.2  | 17.4 | 21.4 |
| FH40-20S-0.5SV(99) | CL580-2105-9-99 | 20                | 10.57                                                                     | 13.2 | 9.5  | 10.5 | 12.1 | 24                               | —    | 11.5 | 13.4 | 10.2 | 25.4 | 29.4 |
| FH40-24S-0.5SV(99) | CL580-2106-1-99 | 24                | 12.57                                                                     | 15.2 | 11.5 | 12.5 | 14.1 | 24                               | —    | 11.5 | 15.4 | 12.2 | 25.4 | 29.4 |
| FH40-30S-0.5SV(99) | CL580-2108-7-99 | 30                | 15.57                                                                     | 18.2 | 14.5 | 15.5 | 17.1 | 32                               | 28.4 | 14.2 | 18.4 | 15.2 | 33.4 | 37.4 |
| FH40-40S-0.5SV(99) | CL580-2107-4-99 | 40                | 20.57                                                                     | 23.2 | 19.5 | 20.5 | 22.1 | 44                               | 40.4 | 20.2 | 23.4 | 20.2 | 45.4 | 49.4 |
| FH40-45S-0.5SV(99) | CL580-2101-8-99 | 45                | 23.07                                                                     | 25.7 | 22.5 | 23   | 24.6 | 44                               | 40.4 | 20.2 | 25.9 | 22.7 | 45.4 | 49.4 |
| FH40-50S-0.5SV(99) | CL580-2100-5-99 | 50                | 25.57                                                                     | 28.2 | 24.5 | 25.5 | 27.1 | 44                               | 40.4 | 20.2 | 28.4 | 25.2 | 45.4 | 49.4 |
| FH40-60S-0.5SV(99) | CL580-2109-0-99 | 60                | 30.57                                                                     | 33.2 | 29.5 | 30.5 | 32.1 | 56                               | 52.4 | 26.2 | 33.4 | 30.2 | 57.4 | 61.4 |
| FH40-64S-0.5SV(99) | CL580-2102-0-99 | 64                | 32.57                                                                     | 35.2 | 31.5 | 32.5 | 34.1 | 56                               | 52.4 | 26.2 | 35.4 | 32.2 | 57.4 | 61.4 |
| FH40-80S-0.5SV(99) | CL580-2103-3-99 | 80                | 40.57                                                                     | 43.2 | 39.5 | 40.5 | 42.1 | 56                               | 52.4 | 26.2 | 43.4 | 40.2 | 57.4 | 61.4 |

|     |             |                    |                        |                                     |
|-----|-------------|--------------------|------------------------|-------------------------------------|
| HRS | DRAWING NO. | EDC-349783-00-00   |                        |                                     |
|     | PART NO.    | FH40-**S-0.5SV(99) |                        |                                     |
|     | CODE NO.    | CL580              | <div><div></div></div> | <div><div>5</div><div>5</div></div> |