








Panel thickness	A
0.5~0.8	35.6
0.9~1.3	36.1
1.4~1.8	36.5
1.9~2.3	36.9



- Note 1 Please use non-radius side for the panel hooking area.
2 Applicable panel thicknessing is 2.3 to 0.5 mm.
3 Consult hirose for the other panel cutout designs than recommended one.
4. Per pack : 100 pieces.
5. UL(File No.E52653),
C-UL(File No.E52653) authorization article



NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
1	PBT	UL94V-0. BLACK	1	PBT	UL94V-0. BLACK
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-H-00004547	DESIGNED TS.MIYAKI
APPROVED : HS. OKAWA	20160601	CHECKED : YN. TAKASHITA	20160601	DESIGNED : TT. OHSAKO	20160601
DESIGNED : TT. OHSAKO	20160601	DRAWN : TT. OHSAKO	20160601	DRAWING NO. EDC-366293-00-00	PART NO. DF51-26DEP-2C
CODE NO. CL543-5082-0-00	1	1	1	1	1