

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard				
Rating	Operating Temperature Range	-55°C to +85°C (Note1)	Storage Temperature Range	-10 °C to +60°C (Note3)
	Operating Humidity Range	20% to 80% (Note2)	Storage Humidity Range	40% to 70% (Note3)
	Voltage	50 V AC/DC	Applicable Connector	DF53-20S-0.6H(##)
Current	All pin	AWG 32 : 0.7A	Applicable Contact	DF53-32SCF
	Any of 2 pins as a power	AWG 32 : 1.3A(power), 0.5A(signal)		

### Specifications

Item	Test method	Requirements	QT	AT
------	-------------	--------------	----	----

#### Construction

General Examination	Visually and by measuring instrument.	According to drawing.	X	X
Marking	Confirmed visually.		X	X

#### Electric Characteristics

Insulation Resistance	100 V DC.	100 MΩ MIN.	X	—
Voltage Proof	200 V AC for 1 min.	No flashover or breakdown.	X	—

#### Mechanical Characteristics

Mechanical Operation	20 times insertion and extraction.	No damage, crack or looseness of parts.	X	—
Mating and unmating Force	It takes out and inserts with a conformity connector.	1.Insertion Force : 25.2N MAX. 2.Extraction Force : 5.6N MIN.	X	—
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.	No damage, crack or looseness of parts.	X	—
Shock	Acceleration 500 m/s <sup>2</sup> duration of pulse 11 ms at 3 times for 3 directions.		X	—
Contact extraction force	Pull out the cable after housing fixation.	3N MIN	X	—

#### Environmental Characteristics

Damp Heat (Steady State)	Exposed at 40 ± 2°C , humidity 90 to 95 % , 96 h. (After leaving the room temperature for 1 to 2h.)	1. Insulation resistance: 100 MΩ MIN. 2.No damage, crack or looseness of parts.	X	—
Rapid Change Of Temperature	Temperature -55°C→ +85°C Time 30min→ 30min Under 5 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)	1. Insulation resistance: 100 MΩ MIN. 2. No damage, crack or looseness of parts.	X	—
Dry Heat	Exposed at 85±2°C, 96h		X	—
Cold	Exposed at -55±3°C, 96h		X	—

Remarks  
 Note 1: Include the temperature rising by current.  
 Note 2: No condensing. Apply to the condition of long term storage for unused products before harness assembly.  
 Note 3: Applicable to unused product packaging.

△	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△	0				

Unless otherwise specified, refer to IEC 60512.	APPROVED	SJ. OKAMURA	20231228
	CHECKED	SZ. ONO	20231228
	DESIGNED	JN. TONAI	20231227
	DRAWN	JN. TONAI	20231227

Note QT:Qualification Test AT:Assurance Test X:Applicable Test DRAWING NO. ELC-380642-00-00

<b>HRS</b>	SPECIFICATION SHEET	PART NO.	DF53-20P-0. 6C		
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0668-1024-0-00	△	2/1