

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	$\triangle 1$ -55°C TO 85°C (NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO 60°C	
	VOLTAGE	$\triangle 1$ 50V AC/DC	APPLICABLE CONNECTOR	BM28B0.6-10DP/2-0.35V	
	CURRENT	SIGNAL CONTACT : 0.3A POWER CONTACT : 5.0A			
<b>SPECIFICATIONS</b>					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
<b>CONSTRUCTION</b>					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
<b>ELECTRIC CHARACTERISTICS</b>					
CONTACT RESISTANCE	20mV AC OR LESS 1kHz,1m A .	Signal contact resistance: 70 mΩ MAX. $\triangle 1$ Power contact resistance: 15 mΩ MAX. $\triangle 1$	X	-	
INSULATION RESISTANCE	100V DC.	50MΩ MIN.	X	-	
VOLTAGE PROOF	150V AC FOR 1 min. $\triangle 1$	NO FLASHOVER OR BREAKDOWN.	X	-	
<b>MECHANICAL CHARACTERISTICS</b>					
MECHANICAL OPERATION	10TIMES INSERTIONS AND EXTRACTIONS.	① Signal contact resistance: 70 mΩ MAX. $\triangle 1$ Power contact resistance: 15 mΩ MAX. $\triangle 1$ ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min, SINGLE AMPLITUDE 0.75 mm, 10CYCLES, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
SHOCK	490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
<b>ENVIRONMENTAL CHARACTERISTICS</b>					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → +85°C TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER : WITHIN 2-3 min)	① Signal contact resistance: 70 mΩ MAX. $\triangle 1$ Power contact resistance: 15 mΩ MAX. $\triangle 1$ ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① Signal contact resistance: 70 mΩ MAX. $\triangle 1$ Power contact resistance: 15 mΩ MAX. $\triangle 1$ ② INSULATION RESISTANCE: 25MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
SULPHUR DIOXIDE	EXPOSED IN 25 PPM FOR 96h, 25°C, 75%. (REFER TO JIS C 60068)	① Signal contact resistance: 70 mΩ MAX. $\triangle 1$ Power contact resistance: 15 mΩ MAX. $\triangle 1$	X	-	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
$\triangle 1$	8	DIS-H-00019757	ST. HIRONAKA	RT. SHIMIZU	20240125
REMARKS			APPROVED	MO. ISHIDA	20170523
NOTE 1: INCLUDE THE TEMPERATURE RISING BY CURRENT			CHECKED	TS. MIYAZAKI	20170523
Unless otherwise specified, refer to JIS C 5402 and IEC 60512.			DESIGNED	RT. SHIMIZU	20170523
			DRAWN	SN. NUMAZAKI	20170523
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-365298-53-00
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	BM28B0.6-10DS/2-0.35V (53)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0673-5044-0-53	$\triangle 1$ 1/1