

Aug. 1. 2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	Operating Temperature Range	-55°C to 125°C(Notes 1)	Storage Temperature Range	-10°C TO 60°C
	Voltage	30V AC/DC	Mating Connector	DF40T*-10DS-0. 4V(**)
	Current	0. 3A		

### SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

<b>CONSTRUCTION</b>				
General Examination	Visually and by measuring instrument.	① According to drawing.	X	X
Marking.	Confirmed visually.		X	X

<b>ELECTRIC CHARACTERISTICS</b>				
Contact Resistance	20mV AC or less 1kHz, 1mA.	① 90mΩ MAX.	X	-
Insulation Resistance	100V DC.	① 50MΩ MIN.	X	-
Voltage Proof	100V AC for 1 min.	① No flashover or breakdown.	X	-



<b>MECHANICAL CHARACTERISTICS</b>				
Mechanical Operation	10times insertions and extractions.	① Contact resistance: 90mΩ MAX. ② No damage, crack or looseness of parts.	X	-
Vibration	Frequency 10 to 500, acceleration 49 m/s <sup>2</sup> . Sweep time 1 oct/min. 8h for 3 axial directions.	① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.	X	-
Shock	Acceleration 980 m/s <sup>2</sup> , duration of pulse 6 ms at 3 times for 3 directions.		X	-

<b>ENVIRONMENTAL CHARACTERISTICS</b>				
Rapid Change of Temperature	Temperature -55 → 125 °C Time 30 → 30 min Under 1000 cycles.	① Contact resistance: 90mΩ MAX. ② No damage, crack or looseness of parts.	X	-
Dry Heat	Exposed at 125 °C, 1,000 h.		X	-
Damp Heat	Exposed at 60 ± 2 °C Relative humidity 90 to 95 %, 1000 h.	① Contact resistance: 90mΩ MAX. ② Insulation resistance: 25 MΩ MIN. ③ No damage, crack or looseness of parts.	X	-
Damp Heat, Cyclic	Exposed at -10 to 65°C, Relative humidity 90 to 96%, 10cycles, total 240h.		X	-
Sulphur Dioxide	Exposed in 25 PPM for 96h, 40°C, Relative humidity 80%.		X	-
Heat Resistance of Soldering	<b>Recommended temperature profile soldering area</b> MAX 250°C, 220°C for 60 seconds MAX. <b>Preheating area</b> 150 to 180°C 90 to 120 seconds. Maximum twice action is allowed under the same condition. <b>Recommended manual soldering condition</b> Soldering iron temperature 350°C. Soldering time: within 3 seconds.	① No deformation of case of excessive looseness of the terminals.	X	-
Solderability	Soldering temperature: 245 ± 5°C Duration of immersion: soldering for 3±0.5 seconds.	A new uniform coating of solder shall cover a minimum of 95% of the surface being immersed.	X	-

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
7	DIS-H-00009674	YK. SATAKE	TS. MIYAZAKI	20210623

REMARKS Note1: Include the temperature rising by current	APPROVED	WR. FUKUCHI	20210303
	CHECKED	TS. MIYAZAKI	20210303
	DESIGNED	YK. SATAKE	20210303
	DRAWN	YK. SATAKE	20210303

Unless otherwise specified, refer to JIS C 5402. IEC 60512.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC-386793-58-00		
	SPECIFICATION SHEET	PART NO.	DF40TC-10DP-0. 4V (58)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0684-4269-0-58	 1/1