

Mar.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	AC/DC 50 V	OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY: 90% MAX (NO DEW CONDENSATION IS PERMITTED)
	CURRENT	0.3A(28pos. side) (*1) 0.5A(10pos. side) (*1)		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION

GENERAL EXAMINATION	VISUAL AND WITH MEASURING INSTRUMENT	ACCORDING TO A DRAWING	X	X
MARKING	CONFIRM VISUALLY		X	X

ELECTRIC CHARACTERISTICS

CONTACT RESISTANCE [EIA-364-23]	100 mA	Row a: 60 mΩ MAX (*1,2) Row b: 70 mΩ MAX (*1.2) Row c: 80 mΩ MAX (*1.2) Row d: 90 mΩ MAX (*1.2)	X	-
INSULATION RESISTANCE [EIA-364-21]	100 V DC	100 MΩ MIN	X	-
VOLTAGE PROOF [EIA-364-20]	150 V AC FOR 1 min	NO BREAKDOWN LEAKAGE CURRENT 2mA OR LESS	X	-

MECHANICAL CHARACTERISTICS

INSERTION AND WITHDRAWAL FORCES [EIA-364-13]	MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE: 0.4N/PIN MAX WITHDRAWAL FORCE: 0.015N/PIN MIN	X	-
MECHANICAL OPERATION [EIA-364-09]	100TIMES INSERTION AND EXTRACTION	1) CONTACT RESISTANCE CHANGE: +10 mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	-
RANDOM VIBRATION [EIA-364-28]	FREQUENCY: 20 TO 500 Hz POWER SPECTRAL DENSITY: 0.02 G ² /Hz FOR 60 min IN THREE DIRECTIONS	1) NO ELECTRICAL DISCONTINUITY OF 1μs OR MORE 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	-

ENVIRONMENTAL CHARACTERISTICS

THERMAL SHOCK [EIA-364-32]	TEMPERATURE(°C): -55 → 20 ~ 35 → 85 → 20 ~ 35 TIME(min): 30 → 5MAX → 30 → 5MAX UNDER 10 CYCLES	1) CONTACT RESISTANCE CHANGE: +10 mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	-
CYCLIC TEMPERATURE AND HUMIDITY [EIA-364-31]	@ 25 °C, 90-95% RH: 120 min DWELL TIME ↓ 120 min RAMP TIME @ 65 °C, 90-95% RH: 120 min DWELL TIME UNDER 60 CYCLES		X	-
DRY HEAT [EIA-364-17]	EXPOSED AT 105°C, 300 HOURS	1) CONTACT RESISTANCE CHANGE: +10 mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	-
DUST [EIA-364-91]	UNMATED 1 HOUR	1) CONTACT RESISTANCE CHANGE: +10 mΩ OR LESS	X	-
MIXED FLOWING GAS [EIA-364-65]	EXPOSED AT 30 °C, 70% RH Cl ₂ : 10 ppb, NO ₂ : 200 ppb, H ₂ S: 10 ppb, SO ₂ : 100 ppb MATED 10 DAYS	1) CONTACT RESISTANCE CHANGE: +10 mΩ OR LESS 2) NO HEAVY CORROSION	X	-

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
⚠	6	DIS-F-00008904	DK. AIMOTO	NH. TAMAI	20210420

REMARK (*1) SPECIFICATION WHEN MATED WITH IT9M3-152P-0.5SH4. (*2) THE VALUE OF CONTACT RESISTANCE INCLUDES THE BULK RESISTANCE.	APPROVED	NH. TAMAI	20191010
	CHECKED	NH. TAMAI	20191010
	DESIGNED	DK. AIMOTO	20191010
	DRAWN	DK. AIMOTO	20191010

NOTE -- QT: QUALIFICATION TEST; AT: ASSURANCE TEST; X: APPLICATION TEST	DRAWING NO.	ELC-379971-00-00
---	-------------	------------------

HRS	SPECIFICATION SHEET	PART NO.	IT9M3-152S-0.5SV4	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0636-1801-0-00	⚠ 1/1