

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C <sup>(1)</sup>		
	VOLTAGE	60 V AC/DC		STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX (NOT DEWED)		
	CURRENT	2 A					
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		x	x
MARKING		CONFIRMED VISUALLY.				x	x
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		1A DC.		10 mΩ MAX.		x	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		10 mV AC MAX, 0.1 mA(DC OR 1000Hz)		10 mΩ MAX.		x	—
INSULATION RESISTANCE		500 V DC.		100 MΩ MIN.		x	—
VOLTAGE PROOF		1000 V AC FOR 1 min.		NO BREAKDOWN.		x	—
MECHANICAL CHARACTERISTICS							
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
VIBRATION		FREQUENCY 20 TO 200Hz (44m/s <sup>2</sup> ) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② CONTACT RESISTANCE: 20 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
SHOCK		981m/s <sup>2</sup> DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
LOCK STRENGTH		MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.		① 100N MIN.		x	—
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 20 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
DRY HEAT		EXPOSED AT 140°C, 120 h.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
COLD		EXPOSED AT -40°C , 120 h.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x	—
RESISTANCE TO SO <sub>2</sub> GAS		EXPOSED IN 25 PPM AT 75% MIN FOR 96h.		① CONTACT RESISTANCE: 20 mΩ MAX.		x	—
RESISTANCE TO SOLDERING HEAT		REFLOW TEMP. OVER 250°C , 10sec. PREHEAT 180°C MAX , 120sec.		NO PLATING PEELING OF THE TERMINALS, MELTINGS OF HOUSINGS.		x	—
SOLDERABILITY		SOLDERED AT SPECIFIED TEMPERATURE PROFILE.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.		x	—
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
△	0						
REMARK				APPROVED	AH. EDASHIGE	20220615	
(NOTE1) "STORAGE" means a long-term storage state for the unused product.				CHECKED	AH. EDASHIGE	20220615	
				DESIGNED	MH. SHOUJI	20220615	
				DRAWN	CHANGSHEN ZHOU	20220615	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC-399090-00-00	
<b>HRS</b>	SPECIFICATION SHEET			PART NO.	ZH05-32DS-2H (B)		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL0756-2111-0-00 △ 1/1		