





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT




PIN ASSIGNMENT
8 7 6 5 4 3 2 1
16 15 14 13 12 11 10 9



RECOMMENDED PCB PATTERN


- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : $150\sim 180^{\circ}\text{C}$ 60~120s
2. TEMPERATURE FOR SOLDERING IRON : $280\sim 300^{\circ}\text{C}$ WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




3	BRASS	TIN PLATED T=0.64	6	PET	
2	BRASS	TIN PLATED T=0.64	5	PS	
1	PPS	BLACK	4	BRASS	TIN PLATED T=0.4
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
		APPROVED : NH. NAKATA	16.03.28	DRAWING NO.	EDC-361741-00-00
		CHECKED : HS. OZAWA	16.03.27	PART NO.	GT25H2-16DP-2.2H
		DESIGNED : TK. SHISHIKURA	16.03.26	CODE NO.	CL775-0089-4-00
		DRAWN : TK. SHISHIKURA	16.03.26		

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKAGING SPECIFICATION



REEL DIMENSION(FREE)



CARDBOARD DIMENSION(FREE)



BOX SIZE

W = (405) (mm)

D = (405) (mm)

H = (49) (mm)

HRS

DRAWING NO.	EDC-361741-00-00
PART NO.	GT25H2-16DP-2.2H
CODE NO.	CL775-0089-4-00

2/2