


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




RECOMMENDED PATTERN




RECOMMENDED METAL MASK THICKNESS : 120μm
RECOMMENDED METAL MASK OPENING RATIO : 80% FOR LEAD PAD



A-A(20:1)



ENGAGEMENT FIGURE (20:1)



HRS DRAWING FOR REFERENCE

NOTES 1. ALL LEADS CO-PLANARITY SHALL BE 0.1mm MAX.
2 IS NO PATTERN AREA OTHER THAN THE SAME CIRCUIT.
3 HRS MARK AND CAV NO. IS INDICATED IN APPROXI POSITION SHOWN.
4 GATE POSITION IS POSITIONED IN APPROXIMAL AREA SHOWN.


NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
2	PHOSPHOR BRONZE	CONTACT AREA:GOLD 0.05μm MIN SMT LEAD :GOLD 0.05μm MIN UNDERPLATING:NICKEL 1μm MIN	6	PS	CLEAR(REINFORCEMENT COLLAR)
			5	PS	BLACK(PLASTIC REEL)
			4	POLYESTER	CLEAR(COVER TAPE)
1	LCP	BLACK,UL94V-0	3	PS	CLEAR(EMBOSSED CARRIER TAPE)


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	10 : 1	△0					

HIROSE ELECTRIC CO., LTD.	APPROVED : WR. FUKUCHI	20201211	DRAWING NO. EDC-317292-58-00
	CHECKED : TS. MIYAZAKI	20201210	PART NO. DF40HC(3.0)-50DS-0.4V(58)
	DESIGNED : RH. KITAGAWA	20201210	
	DRAWN : YK. MITSUISHI	20201209	CODE NO. CL0684-4099-2-58 △0 1/2


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


EMBOSSED CARRIER TAPE PACKAGING (5:1)






DIRECTION OF UNREELING






7 TAPING(FREE)

STYLE AND DIMENSION OF REEL (FREE SIZE)



D-D (FREE)



NOTES
5. PER REEL 1000 CONNECTORS.
6. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
7. REFER TO JIS C 0806, IEC 60286-3. (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)
8. AFTER PACKAGING, ROLL 2 METERS OF THE REINFORCEMENT COLLAR TO OUTER CIRCUMFERENCE OF TAPE AND REEL POCKET, AND TAPE DOWN AT THE END OF THE COLLAR.

HRS DRAWING FOR REFERENCE

DRAWING NO.	EDC-317292-58-00
PART NO.	DF40HC(3.0)-50DS-0.4V(58)
CODE NO.	CL0684-4099-2-58

△0 2/2