

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	— °C TO — °C			STORAGE TEMPERATURE RANGE	— °C TO — °C			
	VOLTAGE	AC — V , DC — V							
	CURRENT	2 A (WHEN USING APPLICABLE WIRE AWG#24)			APPLICABLE CABLE	AWG#24 TO 28 (INSULATION DIA φ1.4 MAX)			
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			○	○
MARKING		CONFIRMED VISUALLY.						○	○
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A			15 mΩ MAX.			○	—
		CONTACT SHALL BE MEASURED AT DC — A			— mΩ MAX.			—	—
MECHANICAL CHARACTERISTICS									
CONTACT INSERTION AND WITHDRAWAL FORCES		— BY STEEL GAUGE.			INSERTION AND WITHDRAWAL FORCES : — N MAX.			—	—
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.			CONTACT RESISTANCE: 20 mΩ MAX.			○	—
					— RESISTANCE: — mΩ MAX.			—	—
CRIMP TENSILE STRENGTH (CRIMPED CONNECTION)		CRIMPED ONLY CONDUCTOR OF THE APPLICABLE WIRE AND PULLING THE APPLICABLE WIRE.			• AWG#24: 36 N MIN. • AWG#26: 24 N MIN. • AWG#28: 16 N MIN.			○	—
ENVIRONMENTAL CHARACTERISTICS									
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION.			○	—
REMARKS									
Unless otherwise specified, refer to JIS C 5042. Note QT:Qualification Test AT:Assurance Test ○:Applicable Test					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
					E.YUMINO DD.10.5	E.YUMINO DD.10.5	U.Sato DD.10.10	M.Yoshida DD.10.11	
HRS HIROSE ELECTRIC CO., LTD.					SPECIFICATION SHEET			PART NO. RP13-PC-222	
CODE NO. (OLD) CL		DRAWING NO. ELC4-009135			CODE NO. CL 113-0141-7			1 1	

