


Oct.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- Applicable crimping contact :
 Contact No.1 to 11 :RP13A-SC-222 (CL113-0151-0)
 (Applicable wire AWG #24 TO #28)
 Contact No.12 to 13 :RP13A-SC-212 (CL113-0150-8)
 (Applicable wire AWG #18 TO #22)
 - Applicable crimp contact crimping tool :
 RP13A-TC-02(CL150-0071-3)
 Applicable crimp contact extraction tool :
 RP13A-SC-TP(CL150-0022-8)
- ③ The recommended tightening torque of Ref.No. ⑥ shall be 0.2 N·m.
- 4 This product is delivered disassemble.
- 5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.

4	Brass			7	Polyvinylchloride	(Black) UL94V-0	
3	Polycarbonate	(Black) UL94V-0		6	Brass	Black chromate treatment(Trivalent chromium) JIS B1111 M2×0.4×4	
2	Polycarbonate	(Black) UL94V-0		5	Steel	Nickel plating	
1	Polycarbonate	(Black) UL94V-0					
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.				APPROVED :EJ. KUNII 16.05.12 CHECKED :EJ. KUNII 16.05.12 DESIGNED :MM. ISHII 16.05.12 DRAWN :MM. ISHII 16.05.12	DRAWING NO. EDC-010191-71-00 PART NO. RP13A-12PE-13SC(71) CODE NO. CL113-0201-7-71		