

Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60°C <sup>(1)</sup>
	VOLTAGE	△ 60 V AC/DC		STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX
	CURRENT	2 A			(NOT DEWED)
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
<b>CONSTRUCTION</b>					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.			x	x
<b>ELECTRIC CHARACTERISTICS</b>					
CONTACT RESISTANCE	1A DC.		10 mΩ MAX .	x	-
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	10 mV AC MAX, 0.1 mA(DC OR 1000Hz)		10 mΩ MAX .	x	-
INSULATION RESISTANCE	500 V DC.		100 MΩ MIN.	x	-
VOLTAGE PROOF	1000 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	x	-
<b>MECHANICAL CHARACTERISTICS</b>					
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s <sup>2</sup> ) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② CONTACT RESISTANCE: 20 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
SHOCK	981m/s <sup>2</sup> DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.		① 100N MIN.	x	-
<b>ENVIRONMENTAL CHARACTERISTICS</b>					
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 20 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
DRY HEAT	EXPOSED AT 140°C, 120 h.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
COLD	EXPOSED AT -40°C , 120 h.		① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
RESISTANCE TO SO <sub>2</sub> GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.		① CONTACT RESISTANCE: 20 mΩ MAX.	x	-
RESISTANCE TO SOLDERING HEAT	REFLOW TEMP. OVER 260°C , 10sec. PREHEAT 180°C MAX , 120sec.		NO PLATING PEELING OF THE TERMINALS, MELTINGS OF HOUSINGS.	x	-
SOLDERABILITY	SOLDERED AT SPECIFIED TEMPERATURE PROFILE.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.	x	-
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△	1	DIS-T-00006023	YH. MAMADA	HH. TSUKUMO	20200407
REMARK			APPROVED	HK. UMEHARA	20171018
(NOTE1) "STORAGE" means a long-term storage state for the unused product before assembly to PCB.			CHECKED	HK. UMEHARA	20171018
			DESIGNED	TY. ISHIGURO	20171018
			DRAWN	MN. SATOH	20171018
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-373533-00-00
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	ZE05H-16DP-2H	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL752-2114-0-00	△ 1/1