




- Notes
- 1 Applicable crimp contact:
RP13A-SC-222/CL113-0151-0
(Applicable cable size : AWG#24 to #28.
Cable jacket outer diameter shall be $\phi 1.4$ mm or less.)
 - 2 Applicable cable crimping tool : RP13A-TC-01/CL150-0070-0
 - 3 Extraction tool : RP13A-SC-TP/CL150-0022-8
 - 4 The tightening torque of Ref No. ⑥ : 0.15 to 0.2 N·m.
To prevent loosening Ref No. ⑥ , use LOCTITE 243,
HENKEL JAPAN or equivalent.
 - 5 Shall be disassembled when delivered.
 - 6 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.

4	Brass			7	Polyvinylchloride	(Black)
3	Polycarbonate	(Black)	UL94V-0	6	Brass	Black chromate treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
2	Polycarbonate	(Black)	UL94V-0	5	Steel	Nickel plating
1	Polycarbonate	(Black)	UL94V-0			
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00009810		DESIGNED TY. SUZUKI
				CHECKED HY. KOBAYASHI		DATE 20220215
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH		DRAWING NO. EDC-028550-71-71		
		CHECKED : HY. KOBAYASHI		PART NO. RP13A-12PP-15SC(71)		
		DESIGNED : HS. KAWASHIMA		CODE NO. CL0113-1010-4-71		
		DRAWN : WR. AJIRO				