


Oct.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 Applicable crimp contact:
 Contact No.1 to 11 : RP19-PC-222(CL113-0264-7)
 (Wire range, AWG #24 to 28)
 Contact NO.12 to 13 : RP19-PC-212(CL113-0263-4)
 (Wire range, AWG #18 TO 22)
 - 2 Applicable crimp contact crimping tool: RP13A-TC-01(CL150-0070-0)
 Applicable crimp contact extraction tool: RP6-SC-TP(CL150-0039-0)
 - 3 The recommended clamp torque of Ref.No. ⑥ to 0.2 N·m.
 - 4 This product is delivered disassembled.
 - 5 The cable clamp strength, rotation strength and other
 Please confirm before the use.

4	BRASS		8	Stainless steel	
3	POLYCARBONATE	(BLACK) UL94V-0	7	Flexible polyvinylchloride	(BLACK) UL94V-0
2	POLYCARBONATE	(BLACK) UL94V-0	6	BRASS	ZINC PLATING BLACK CHROMETE TREATMENT (TRIVALENT CHROMIUM) JIS B 1111 M2X0.4X4
1	POLYCARBONATE	(BLACK) UL94V-0	5	STEEL	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm	SCALE 2 : 1	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.			APPROVED :EJ. KUNII 16.03.23 CHECKED :EJ. KUNII 16.03.23 DESIGNED :MM. ISHII 16.03.23 DRAWN :MM. ISHII 16.03.23	DRAWING NO. EDC-027897-71-00 PART NO. RP13A-12PA-13PC(71) CODE NO. CL113-4003-5-71	1/1	