




- Notes
- 1 Applicable crimp contact:
RP19-PC-222/CL113-0264-7
(Applicable cable size : AWG#24 to #28.
Cable jacket outer diameter shall be $\phi 1.15\text{mm}$ or less.)
 - 2 Applicable cable crimping tool : RP13A-TC-01/CL150-0070-0
 - 3 Extraction tool : RP6-SC-TP/CL150-0039-0
 - 4 The tightening torque of Ref No. ⑥ : 0.15 to 0.2 N·m.
To prevent loosening Ref No. ⑥, use LOCTITE 243, HENKEL JAPAN or equivalent.
 - 5 Shall be disassembled when delivered.
 - 6 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.

4	Brass		8	Stainless steel	
3	Polycarbonate	(BLACK) UL94V-0	7	Polyvinylchloride	(BLACK) UL94V-0
2	Polycarbonate	(BLACK) UL94V-0	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
1	Polycarbonate	(BLACK) UL94V-0	5	Steel	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm	SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00009810	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20220215
HRS HIROSE ELECTRIC CO., LTD.			APPROVED : EJ. KUNII 20160323	DRAWING NO. EDC-028107-71-00		
			CHECKED : EJ. KUNII 20160323	PART NO. RP13A-12PK-13PC(71)		
			DESIGNED : MM. ISHII 20160323	CODE NO. CL0113-4006-3-71		
			DRAWN : MM. ISHII 20160323	1/1		