

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽¹⁾	
	VOLTAGE	60 V AC/DC	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX (NOT DEWED)	
	CURRENT	2 A			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING		CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		1A DC.	10 mΩ MAX .	—	—
CONTACT RESISTANCE		10 mV AC MAX, 0.1 mA(DC OR 1000Hz)	10 mΩ MAX .	—	—
MILLIVOLT LEVEL METHOD					
INSULATION RESISTANCE		500 V DC.	100 MΩ MIN.	×	—
VOLTAGE PROOF		1000 V AC FOR 1 min.	NO BREAKDOWN.	—	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
VIBRATION		FREQUENCY 20 TO 200Hz (44m/s ²) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② CONTACT RESISTANCE: 20 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— — ×	— — —
SHOCK		981m/s ² DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
LOCK STRENGTH		MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.	① 100N MIN.	×	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 20 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— — —
RAPID CHANGE OF TEMPERATURE		TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
DRY HEAT		EXPOSED AT 140°C, 120 h.	① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
COLD		EXPOSED AT -40°C , 120 h.	① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
RESISTANCE TO SO ₂ GAS		EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	① CONTACT RESISTANCE: 20 mΩ MAX.	—	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	0				
REMARK			APPROVED	AH. EDASHIGE	20220615
(NOTE1) "STORAGE" means a long-term storage state for the unused product.			CHECKED	AH. EDASHIGE	20220615
			DESIGNED	MH. SHOUJI	20220615
			DRAWN	CHANGSHEN ZHOU	20220615
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-399092-00-00	
	SPECIFICATION SHEET		PART NO.	ZH05-32DP-HU (B)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0756-2219-0-00	 1/1