





Jan.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C (Note 1)		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C(Note 2)
	VOLTAGE	60 V AC/DC		STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX
	CURRENT	2 A			(NOT DEWED)
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 1 mA(DC OR 1000Hz)		30 mΩ MAX .	-	-
INSULATION RESISTANCE	100 V DC.		500 MΩ MIN.	X	-
VOLTAGE PROOF	300 V AC FOR 1 min.		NO BREAKDOWN.	-	-
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	10 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
VIBRATION	FREQUENCY 5 TO 600Hz (5 TO 14.9Hz:16.5mm(p-p), 14.9 TO 600Hz:73.0m/s ²) AT 3h FOR 8 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② CONTACT RESISTANCE: 50 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
SHOCK	500m/s ² DURATION OF PULSE 10ms AT 10 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.		① 25 N MIN	X	-
ENVIRONMENTAL CHARACTERISTICS 					
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE:500 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -40→5 TO 35→125→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
DRY HEAT	EXPOSED AT 125°C, 1000 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
COLD	EXPOSED AT -40°C, 1000 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	1	DIS-T-00013143	YT. TAKANASHI	OM. MIYAMOTO	20220303
REMARK			APPROVED	HK. UMEHARA	20200806
(NOTE1) Include the temperature rising by current.			CHECKED	OM. MIYAMOTO	20200805
(NOTE2) Apply to the condition of long term storage for unused products before harness assembly. After harness assembly, operating temperature and humidity range is applied for interim storage during transportation.			DESIGNED	YT. TAKANASHI	20200805
			DRAWN	GY. YOON	20200805
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-392586-00-00
	SPECIFICATION SHEET		PART NO.	GT50-2S-1C	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0760-1003-0-00	 1/1