




- Notes
- ① Plating (Ref. No. ②, ③)
Contact area : gold plating 0.2 μ m min.
Lead area : gold plating flash.
Under plating : nickel plating 2 μ m min.
 - ② Recommended tightening torque of Ref. No. ⑥ : 0.45~0.5N $\cdot$ m.
To prevent loosening, apply LOCTITE 263 and LOCK PRIMER 7649 manufactured by HENKEL JAPAN Co., Ltd. according to the Loctite Coating Procedure Manual (ETAD-C0151-00).
 - 3 Applicable jigs
Solder termination fixture : HR30-7J-12PC-T01 (CL150-0230-5)
Tightening collar for back shell (Ref. No. ⑧) : HR30-8P-T02 (CL150-0224-2)
 - 4 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure.
Please confirm before the use.
 - ⑤ The assembly this product applies to the manual ETAD-C0476-00.

4	PPS	(Black)	UL94V-0	8	PPS	(Black)	UL94V-0
3	Copper alloy			7	CR	(Black)	
2	Copper alloy			6	Polyacetal	(Natural)	
1	PPS	(Black)	UL94V-0	5	PBT	(Black)	UL94V-0
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS	

UNITS mm		SCALE 5 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00014969		DESIGNED HY. KISHI	CHECKED HY. KOBAYASHI	DATE 20230404
HIROSE ELECTRIC CO., LTD.		APPROVED . MO. SATOH	20051021	DRAWING NO. EDC3-113842-71				
		CHECKED . MO. SATOH	20051021	PART NO. HR30-7J-12P(71)				
		DESIGNED . EJ. KUNII	20051021	CODE NO. CL0130-2020-9-71				
		DRAWN . EJ. KUNII	20051021	1				