








Dec.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV. RoHS COMPLIANT



HRS DRAWING FOR REFERENCE


- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.) USED REFLOW SYSTEM**
- NO. OF CYCLES : 2 MAX
 - PEAK : 250°C
 - OVER 230°C : 20~40s
 - PREHEAT : 150~180°C
 - : 90~120s
- △ 2. TEMPERATURE FOR SOLDERING IRON : 350~380°C WITHIN 5s**
- 3. CO-PLANARITY : 0.1mm MAX**
- 4. RECOMMENDED SOLDER THICKNESS : 0.10mm**



| 3 | BRASS | TIN PLATING | 6 | POLYSTYRENE | | | |
|--------------------------------------|----------|-------------|---------|------------------------------|----------|--------------------------|---------|
| 2 | BRASS | Au PLATING | 5 | POLYESTER | | | |
| 1 | LCP | BLACK | 4 | POLYSTYRENE | | | |
| NO. | MATERIAL | FINISH | REMARKS | NO. | MATERIAL | FINISH | REMARKS |
| UNITS | | SCALE | | COUNT | | DESCRIPTION OF REVISIONS | |
| mm | | 5:1 | | 3 | | DIS-T-00020330 | |
| APPROVED : AH. EDASHIGE 2023. 10. 12 | | | | DRAWING NO. EDC-392593-00-00 | | | |
| CHECKED : HH. TSUKUMO 2023. 10. 12 | | | | PART NO. GT50-12P-1H | | | |
| DESIGNED : RS. TAKAGI 2023. 10. 11 | | | | CODE NO. CL0760-1010-0-00 | | | |
| DRAWN : RS. TAKAGI 2023. 10. 11 | | | | | | | |

Dec.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKING STYLE (FREE)



※Embossed pocket has a different shape to prevent overlapping, and the drawing shows a representative shape.

| | | | |
|------------|-------------|------------------|-----|
| HRS | DRAWING NO. | EDC-392593-00-00 | 2/2 |
| | PART NO. | GT50-12P-1H | |
| | CODE NO. | CL0760-1010-0-00 | |
| | NO. | | |