

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +100 °C		STORAGE TEMPERATURE RANGE	-40 °C TO +85 °C		
	VOLTAGE	AC 250 V , DC 350 V					
	CURRENT	12 A		APPLICABLE CABLE			
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X	X
MARKING		CONFIRMED VISUALLY.				X	X
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A		5 mΩ MAX.		X	—
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.		X	—
VOLTAGE PROOF		2000 V AC. FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		X	—
IMPULSE VOLTAGE PROOF		4kV STANDARD WAVE(1.2/50μs VOLTAGE WAVE) FOR POSITIVE VOLTAGE 3 TIMES AND NEGATIVE VOLTAGE 3 TIMES.		NO FLASHOVER OR BREAKDOWN.		X	—
MECHANICAL CHARACTERISTICS							
CONTACT INSERTION AND WITHDRAWAL FORCES		φ0.97±0.003 BY STEEL GAUGE.		INSERTION AND WITHDRAWAL FORCES : 0.2 N MIN.		X	—
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR. (WITH LOCK)		INSERTION AND WITHDRAWAL FORCES : 5 TO 80 N. (CONTACT PORTION:TIN-LEAD PLATING) 5 TO 50 N. (CONTACT PORTION:GOLD PLATING)		X	—
MECHANICAL OPERATION		100 TIMES INSERTIONS AND EXTRACTIONS.		CONTACT RESISTANCE: 10 mΩ MAX.		X	—
VIBRATION		FREQUENCY: 10 TO 55 Hz (1CYCLE : 5min), SINGLE AMPLITUDE 0.75 mm, AT 10CYCLES, FOR 3 DIRECTIONS.		①NO ELECTRICAL DISCONTINUITY OF 10μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	—
SHOCK		490 m/s ² DURATIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		①NO ELECTRICAL DISCONTINUITY OF 10μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	—
CONTACT RETENSION FORCE		APPLYING A PULL FORCE THE WIRE AFTER THE APPLICABLE CRIMPED CONTACT IS ASSEMBLED WITH THE BODY.		50 N MIN.		X	—
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.		①INSULATION RESISTANCE: 10 MΩ MIN (AT HIGH HUMIDITY). ②INSULATION RESISTANCE: 100 MΩ MIN (AT DRY). ③NO DAMAGE, CRACK AND LOOSENESS OF ARTS.		X	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -40→ R/T ⁽¹⁾ → +100 → R/T °C TIME 30 → 10 TO 15 → 30 → 10 TO 15 min UNDER 5 CYCLES.		①INSULATION RESISTANCE: 1000 MΩ MIN. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48h.		NO HEAVY CORROSION RUIN THE FUNCTION.		X	—
DRY HEAT		EXPOSED AT + 100 °C , 96 h.		NO DAMAGE, CRACK AND LOOSENESS OFPARTS.		X	—
COLD		EXPOSED AT - 40 °C , 96 h.		NO DAMAGE, CRACK AND LOOSENESS OFPARTS.		X	—
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
Δ							
REMARK NOTE 1. (1)R/T:ROOM TEMPERATURE. 2. ABOVE SPECIFICATIONS SHOWS THE VALVE IN ASSEMBLED CONDITION WITH APPLICABLE CRAMP CONTACT. Unless otherwise specified, refer to IEC 60512.				APPROVED	EJ. KUNII	16.02.17	
				CHECKED	EJ. KUNII	16.02.17	
				DESIGNED	SJ. SHIMIZU	16.02.17	
				DRAWN	SJ. SHIMIZU	16.02.17	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC-112083-72-00	
HRS	SPECIFICATION SHEET			PART NO.	HR31-5.08P-5SC(72)		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL131-0002-2-72 Δ 1/1		