
FLYER

TM11R Series

FCC Standard, Modular Jack Connector for EMI Prevention

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.




RJ-45 | DIP | EMI Prevention

Features

1. **Shield provides EMI prevention**
2. **Complies with US FCC Standard requirements**
3. **Space-saving 8 pin x 4-port type available**
4. **Compact with a mounted height of 11.9mm from the board surface, 14.6mm width and 17.6mm depth**

Application Examples

- **Industrial PC, LAN, HUB, Interphone, Computer, etc.**



Product Number Structure

- **Jack : TM11 (1) R (2) – 5L (3) – 8 (4) 8 (5)**

1 Series Name	TM11 Series
2 Connector Type	R···Jack
3 Jack Type Number	3C ··· Straight THT 5C ··· Right Angle THT 5L ··· Right Angle THT (Space-saving) 5N2 ··· Right Angle THT (CAT.5 Compatible)
4 Jack Mating Port Size	6 ··· 6 Contacts 8 ··· 8 Contacts 32 ··· 8 Contacts/4-port
5 No. of Inserted Contacts	6 ··· 6 Contacts 8 ··· 8 Contacts 32 ··· 8 Contacts x 4-port = 32 Contacts

Specifications

Rated Current	0.5A
Rated Voltage	125V AC
Operating Temperature	-55 to +85°C*
Contact Resistance	230mΩ Max. (0.1A DC)
Withstanding Voltage	500V AC for 1 min.
Insulation Resistance	100MΩ Min. (100V DC)
Mating Durability	200 times

*Includes temperature rise due to current flow.

- RoHS compliant

HIROSE ELECTRIC CO.,LTD.

MKT-E-21070F Issued: May 10, 2022 © 2022 HIROSE ELECTRIC CO., LTD. All rights reserved. Specifications herein are subject to change without notice. Contact Hirose for latest specifications, drawings, or availabilities.