










May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT

NOTES


- 1) RECOMMENDED REFLOW PROFILE (SEE RIGHT GRAPH)
CYCLE TIME: UP TO 2 CYCLES OF REFLOW SOLDERING ARE POSSIBLE UNDER THE CONDITIONS, PROVIDED THAT THERE IS A RETURN TO NOMAL TEMPERATURE BETWEEN THE FIRST AND SECOND CYCLE.
PEAK TEMPERATURE: 250℃
230℃ MIN. FOR 20 TO 40 SECONDS.
PREHEATING AREA 150 TO 180 ℃ FOR 60 TO 120 SECONDS.
- 2) HAND SOLDERING: 280-300℃, 2S MAX.
- 3) CONTACT COPLANARITY: 0.1mm MAX.
- 4) RECOMMENDED THICKNESS OF PCB: 1.2mm
- 5) RECOMMENDED THICKNESS OF SOLDERING PASTE: 0.12mm
- 6) THIS PRODUCT CAN REPLACE CL767-0175-0-14 GT17HN-4DP-2H(B)(14).



IN COMBINATION WITH STRAIGHT CONNECTOR



IN COMBINATION WITH RIGHT-ANGLE CONNECTOR

2	PA	GREEN		4	BRASS	TIN PLATING			
1	COPPER ALLOY	TIN PLATING		3	BRASS	TIN PLATING			
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS			
UNITS mm		SCALE 2 : 1	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
									
 HIROSE ELECTRIC CO., LTD.			APPROVED : KI. HIROKAWA	20200409	DRAWING NO. EDC-169397-57-00				
			CHECKED : EJ. WAKATSUKI	20200409	PART NO. GT17HN2-4DP-2H(B)(57)				
			DESIGNED : TS. KUBOTA	20200325	CODE NO.				
			DRAWN : YK. MITSUISHI	20200319	CL767-0294-9-57				
						1	2		

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

