



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV. RoHS COMPLIANT












NOTES
1) CONTACT COPLANARITY: 0.1mm MAX.
2) RECOMMENDED THICKNESS OF SOLDERING PASTE: 0.12mm
3) RECOMMENDED REFLOW PROFILE (SEE RIGHT GRAPH)
   CYCLE TIME: UP TO 2 CYCLES OF REFLOW SOLDERING ARE POSSIBLE UNDER THE CONDITIONS, PROVIDED THAT THERE IS A RETURN TO NOMAL TEMPERATURE BETWEEN THE FIRST AND SECOND CYCLE.
   PEAK TEMPERATURE: 250℃
   230℃ MIN. FOR 20 TO 40 SECONDS.
   PREHEATING AREA 150 TO 180 ℃ FOR 60 TO 120 SECONDS.
4) HAND SOLDERING: 280-300℃, 2S MAX.
5) RECOMMENDED THICKNESS OF PCB: 1.6mm
6) FOR THE PREVENTION EXCESSIVE STRESS FOR CONNECTOR AND PCB, WE RECOMMEND ADDITIONAL SUPPORT MECHANISM IF THE FLANGE WAS ELIMINATED.






HRS DRAWING FOR REFERENCE


RECOMMENDED PCB LAYOUT




IN COMBINATION WITH STRAIGHT CONNECTOR



IN COMBINATION WITH RIGHT-ANGLE CONNECTOR



RECOMMENDED PANNEL LAYOUT



NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
2	PA	GREEN	4	BRASS	TIN PLATING
1	COPPER ALLOY	TIN PLATING	3	BRASS	TIN PLATING


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	1	1	DIS-T-00006678	TS. KUBOTA	EJ. WAKATSUKI	20200909


APPROVED	KI. HIROKAWA	20200409	DRAWING NO. EDC-169397-58-00
CHECKED	EJ. WAKATSUKI	20200409	PART NO. GT17HN2-4DP-2H(B)(58)
DESIGNED	TS. KUBOTA	20200325	CODE NO. CL767-0294-9-58
DRAWN	YK. MITSUISHI	20200319	1/2

HIROSE ELECTRIC CO., LTD.


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

REEL DIRECTION







HRS DRAWING FOR REFERENCE



E(5:1)





PACKAGE STYLE
300PCS/REEL

DRAWING NO.	EDC-169397-58-00
PART NO.	GT17HN2-4DP-2H(B)(58)
CODE NO.	CL767-0294-9-58

1 2/2

FORM HC0011-5-8