




Features


- 1 Low profile RF connector (Mated height : 1.2mm Max.)
- 2 Prevention of plug deformation at removal and improved mating retention force
- 3 Easy to check the mounting direction using the polarity key
- 4 Solder wicking / Flux penetration prevention
- 5 Excellent high frequency performance
- V.S.W.R : 1.3 Max. (0 to 3GHz)
1.5 Max. (3 to 6GHz)
1.6 Max. (6 to 8GHz)
- 6 Pick & Place Mounting



Dimensions

Receptacle


[K.FL2-R-SMT-1]



Plug (RF cable type)


[K.FL2-LP-***]

<Double Ended Harness>
OKFL22LP-044H1TS-A100 : ø0.64mm
OKFL2-2LP-04H1T-A-100 : ø0.81mm




Header (Board-to-FPC type)

[K.FL2-PR-SMT09]



Variations of Mating



K.FL2 has 2 mating variations:

- 1) Receptacle + Plug (Cable type)
- 2) Receptacle + Header (Board-to-FPC type)

Specifications

Contact Resistance	20mΩ Max.
Withstanding Voltage	200V AC for 1 min.
Insulation Resistance	500MΩ Min. (100V DC)
Mating Durability	20 times
Characteristic Impedance	50Ω
V.S.W.R.	1.3 Max. : 0 to 3GHz 1.5 Max. : 3 to 6GHz 1.6 Max. : 6 to 8GHz

- RoHS compliant, Halogen-free product*

*This product satisfies halogen free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1500ppm maximum total of chlorine and bromine

Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

