


Nov.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 Applicable crimping contact: RP13-PC-222(CL113-0141-7)  
(Applicable wire: AWG #24 to 28 , Jacket diameter  $\phi$ 1.4Max.)
  - 2 Applicable crimp contact extraction tool: RP13-PC-TP(CL150-0021-5)
  - 3 Applicable crimp contact crimping tool: RP13A-TC-01(CL150-0070-0)(Hole diameter  $\phi$ 7.3)
  - 4 The recommended clamp torque of Ref.No. ⑥ : 0.2 to 0.3 N·m.
  - 5 This product is delivered disassembled.
  - 6 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. please confirm before the use.

3	Polycarbonate	(Black)	UL94V-0	6	Brass	Black chromate treatment(Trivalent chromium) JIS B1111 M2×0.4×4
2	Polycarbonate	(Black)	UL94V-0	5	Flexible polyvinylchloride	(Black)
1	Polycarbonate	(Black)	UL94V-0	4	Brass	
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
HIROSE ELECTRIC CO., LTD.				APPROVED :EJ. KUNII 16.05.31 CHECKED :EJ. KUNII 16.05.31 DESIGNED :MM. ISHII 16.05.31 DRAWN :MM. ISHII 16.05.31	DRAWING NO. EDC-020625-71-00 PART NO. RP13A-12JD-13PC(71) CODE NO. CL113-0205-8-71			1/1