




Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 Total length becomes 28.8 ± 1 when Ref.No. ⑥ is screwed into Ref.No. ① completely.
 - 2 The recommended clump torque of Ref.No. ⑥ to be $0.45 \sim 0.5 \text{ N} \cdot \text{m}$.
To prevent loosening, apply LOCTITE 263 and LOCK PRIMER 7649 manufactured by HENKEL JAPAN Co., Ltd. according to the Loctite Coating Procedure Manual (ETAD-C0151-00).
Spacer for assembly is available HR30-6P-T02.
 - 3 Table for assembly and soldering is available HR30-6R-6P-T01.
 - 4 Surface plating : gold plating $0.2 \mu\text{m}$ min.
Under plating : nickel plating $2 \mu\text{m}$ min.
 - 5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure.
Please confirm before the use.
 - 6 The assembly this product applies to the manual ETAD-C0476-00.

△ CAD change

3	PPS	(Black) UL94V-0	6	PBT	(Black) UL94V-0
2	Brass	4	5	CR	(Black)
1	PPS	(Black) UL94V-0	4	Polyacetal	(Natural:Milky white) △
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 5:1	COUNT △ 2	DESCRIPTION OF REVISIONS DIS-C-00014690	
HIROSE ELECTRIC CO., LTD.		APPROVED :	HY. KOBAYASHI	2018. 02. 26	DRAWING NO.
		CHECKED :	HY. KOBAYASHI	2018. 02. 26	PART NO.
		DESIGNED :	DS. MATSUNE	2018. 02. 26	NO.
		DRAWN :	DS. MATSUNE	2018. 02. 26	CODE NO.
					EDC-112103-31-00
					HR30-6J-6P (31)
					CL0130-2009-6-31
					△ 3 1 1