





	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△	2	DIS-C-000633	H.Z	K.E	07.05.30	△					. .
△					. .	△					. .
△					. .	△					. .





MATING CONDITION(1:1)  
( WHEN REF.NO.(1) IS FASTENED )



- NOTES
- ① THE RECOMMENDED TIGHTENING TORQUE OF REF NO. ③: 0.9 TO 1 N·m.  
THE RECOMMENDED ADHESIVE OF REF NO. ③: LOCTITE 242 MADE BY HENKEL JAPAN LTD.
  - ② THE RECOMMENDED TIGHTENING TORQUE OF REF NO. ⑪: 0.9 TO 1 N·m.  
THE RECOMMENDED ADHESIVE AND PRIMER OF REF NO. ⑪: LOCTITE 242 AND LOCK PRIMER 7649 MADE BY HENKEL JAPAN LTD.
  - 3 CABLE CLAMP STRENGTH AND WATERPROOF PERFORMANCE DEPEND ON CABLE STRUCTURE  
SUCH AS THE JACKET MATERIAL AND HARDNESS.  
WE RECOMMEND CHECKING THE PERFORMANCE BEFORE THE USAGE.
  - 4 ROTATION EXAMPLES ARE SHOWN FOR REF.NO. ①, ③, ⑧, AND ⑪.
  - 5 THE RECOMMENDED CABLE: UL20276-SB(FLEX)5×23AWG+1P×25AWG MADE BY HITACHI CABLE LTD.
  - 6 CONDUIT IS NOT APPLICABLE TO THIS CONNECTOR.
  - △ 7 MAKE SURE THAT ➡ MARKING IS POSITIONED WITHIN 1 FROM THE CENTER OF CONNECTOR  
AS SHOWN IN FIG.1. WHEN MATED TO THE APPLICABLE RECEPTACLE, OTHERWISE,  
THE CONNECTORS ARE NOT COMPLETELY MATED, AND INSERT THIS PLUG TO THE RECEPTACLE  
TO THE END UNTIL THE ➡ MARKING IS LOCATED IN THE CENTER OF THE CONNECTOR.

6	FLUORO RUBBER	(BLACK)			
5	PHOSPHOR BRONZE	NICKEL PLATING	11	PPS	(BLACK) UL94V-0
4	STAINLESS STEEL		10	POLYAMIDE	(WHITE) UL94V-0
3	ZINC ALLOY	BLACK CHROME PLATING	9	HYDROGENATION ACRYLONITRILE BUTADIENE RUBBER	(BLACK)
2	ZINC ALLOY	BLACK CHROME PLATING	8	ALUMINIUM ALLOY	BLACK CHROMATE TREATMENT (TRIVALENT CHROMIUM)
1	PPS	(BLACK) UL94V-0	7	FLUORO RUBBER	(BLACK)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL		DRAWN H. NAGANO 06.09.25	DESIGNED H. NAGANO 06.09.25	CHECKED E. KUNITI 06.09.25	APPROVED M. SATO 06.09.26	RELEASED . .
		DRAWING NO. EDC3-115195		PART NO. HR34B-12WLPB-10SC		
SCALE 2 : 1		 HIROSE ELECTRIC CO., LTD		CODE NO. CL134-0029-8		1/1
UNITS						